







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



PCBLAYOUT
TOL:±0.05

NOTES

MATERIAL

- 1.HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.
- 2.CONTACT MATERIAL: PHOSPHOR BRONZE Ø0.46mm.
- 3.PLATING: GOLD FLASH PLATING OVER NICKEL.

ELECTRICAL

- 1.VOLTAGE RATING: 125 VAC RMS.
- 2.CURRENT RATING: 1.5 AMP.
- 3.CONTACT RESISTANCE: 40 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC

5.DIELECTRIC DIELECTRIC

RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL

- 1.DURRABILITY: 750 CYCLES MIN.
2. MATING/UNMATING FORCE: 2.24 KG.F MAX.

ENVIRONMENTAL:

- 1.STORAGE: -40℃~+85℃.
- 2.OPERATION: -40℃~+85℃.

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.35	X':±3"	PART NO. RJ45-1003-32P	TITLE: 5623 1X4全塑无灯DIP		
X.X:±0.25	X.X':±2"		MANUFACTURE DWG		
X.XX:±0.15	X.XX':±1"				
UNITS	mm	DESIGN:	Ethan		
MATERILA	— — —	CHED:	Olvia		
FINISH	— — —	APPD:	Ava		
				SCALE	SHEET
				N:A	1/1