



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.9.26	阿树



2 Pin 视图




■SPECIFICATIONS

- Voltage rating:250V AC/DC
- Current rating:3A AC/DC
- Withstanding Voltage:800V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤10mΩ
- After environmental testing:≤20mΩ

PART NO.:

X2026 W R-2xXX S-9T SN
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:R-Stright 90°
④Row No.Pin No:2xXX-2x02~2x20Pin
⑤Special No:S-With Positioning baffles on both side
⑥Material:9T-PA9T UL94V-0
⑦Planting: SN-Bright tin plating



PCB LAYOUT

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	6.00	2.00	12	26.00	22.00
03	8.00	4.00	13	28.00	24.00
04	10.00	6.00	14	30.00	26.00
05	12.00	8.00	15	32.00	28.00
06	14.00	10.00	16	34.00	30.00
07	16.00	12.00	17	36.00	32.00
08	18.00	14.00	18	38.00	34.00
09	20.00	16.00	19	40.00	36.00
10	22.00	18.00	20	42.00	38.00
11	24.00	20.00	/		

X2026WR-2xXXS-9TSN	PA9T	Brass	X2026H
PART NO	Material	Material(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: 2.00mm Crimp Style Connector
CHECKED		UNIT:	mm/in	PART NO.: X2026WR-2xXXS-9TSN
APPROVED		SIZE:	A4	DWG NO.: