






RoHS



MICRO SIM CARD



SIM pin assignment	
PIN#	Name
C1	VCC供电电压
C2	RST重置
C3	CLK时钟
C5	GND接地
C6	VPP程序电压
C7	I/O输入输出
CD	Detect Switch



RECOMMENDED P.C.B HOLE LAYOUT
COMPONENT SIDE VIEW(TOLERANCE: +/-0.05)

Specifications/技术规格:

- 1.Current rating/额定电流: 0.5mA
- 2.Voltage rating/额定电压: 50V AC/DC
- 3.Insulation Resistance/绝缘电阻: 100MΩ Min
- 4.Dielectric Withstanding/耐电压: 500V AC/minute
- 5.Contact Resistance/接触电阻: 100mΩ Max
- 6.Durability/耐久性: 5,000 Insertions
- 7.Operating Temperature/工作温度: -40℃ to +85℃

⑤	Spring		1	SUS	Ni Plated
④	Contact point		6	Phosphor bronze	Au Plated
③	Terminal		6	Phosphor bronze	Sn Plated
②	Cover		1	SUS	
①	Base		1	LCP	Black
NO.	Name	Number	Qty	Materil	Remarks


YUANDI® Yuandi Electronics Co.,Ltd

design	date	name	MICRO SIM CARD CONNECTOR
Review	date	model	MICRO-SIM-003A
Approved	date		


Drawing number: A4

RoHS



客户拉出方向



客户拉出方向



如图所示用胶带密封纸箱



YUANDI® Yuandi Electronics Co.,Ltd
元迪

design	date	name
Review	date	
Approved	date	

model MICRO-SIM-003A

Drawing number: 1:1 unit mm gape number A4

modify Review Approved

Tolerance not specified

Proportion

1:1

unit

mm

gape number

A4