



REV.	ECN NO.	REVISED	DATE

NOTE:
1.MATERIAL:
a.HOUSING:ABS BLACK
b.SPRING:SPRING WIRE
(SURFACE PLATING: Ni-PLATING)
SEE ORDERING INFORMATION
2.ELECTRIC:
a.DIELECTNIC VOLTAGE: 270V AC ONE MINUTE
b.OPERATING TEMPERATURE: -10° C~ +80° C

ORDERING INFORMATION
BH-AAA-B5BJ003-130

电池盒

电池型号

SMT 180° TYPE



PLATING:
A-Au1U"
J-Ni-PLATING
K-Sn-PLATING

MATERIAL:
1A-PP BLACK
1B-PA66 BLACK
2A-PPA BROWN
2B-PPA BLACK
3A-PPS BROWN
3B-PPS BLACK
4A-LCP WHITE
4B-LCP BLACK
5B-ABS BLACK



SECTION A-A

Install the upper cover



UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	WangHeng	DATE	2024-11-14
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2024-11-14
X.X :±0.25	X.X :±0.5°	APVD	XueShunYong	DATE	2024-11-14
X.XX :±0.20					
X.XXX :±0.10					
WEIGHT:		SCALE:	SIZE: A4	VIEW:	⊙ ⊞
SHEET 1 OF 1		UNIT: mm	REV.: A/1	OBJECT: MY	

2	SPRING	2	SPRING WIRE	Ni-Plating
1	HOUSING	1	ABS	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR