


SPECIFICATIONS:
Current rating:3.0A AC/DC
Voltage rating:250V AC/DC
Contact resistance:30m ohm MAX
Insulation resistance:5000M ohm MIN
Withstanding voltage:1000V AC for one minute
Operating temperature range:-40°C~+85°C

MATERIAL AND FINISH
 Insulator:PBT+30%G.F(UL94V-0)
 Contact:Copper Alloy, Nickel Undercoated Selective Gold Plated
 Shell:Metal Iron. With Tin Plated



Z-SUB HB * F * * 7 * * *

B=15PIN
D=26PIN
F=44PIN
G=62PIN
H=78PIN

HOUSING TYPE
F=Female

MOUNTING OPTIONS-

1=RIVETED W/SHIELD

2=RIVETED W/FRONT RIVET
3=RIVETED W/REAR RIVET
4=RIVETED W/FRONT RIVET
REAR RIVET

 NUT POST HEIGHT(H)
0=5.8mm
1=4.8mm

— MARK
0=NO LOGO
1=NEXTRON LOGO


—INSULATOR COLOR
0=BLACK
6=BLUE
9=WHITE

—INSULATOR MATERIAL
0=PBT
2=NYLON


— CONTACT PLATED:(CONTACT AREA)

A=GOLD 1u"/Light Tin
B=GOLD 3u"/Light Tin
C=GOLD 5u"/Light Tin
E=GOLD 15u"/Light Tin
F=GOLD 30u"/Light Tin

— CONTACTS MATERIAL
7=PHOSPHOR BRONZE



Mounting Options



UNITS:		SIZE:		NAME:		 NEXTRONICS ENGINEERING CORP.									
■ mm □ inch		A3													
GENERAL TOLERANCE: (UNLESS SPECIFIED)				D-SUB HB TYPE FEMALE		TITLE: CUSTOMER DWG									
		mm	inch	PART NO: Z-SUBHBXFXX7XXXX		DWG NO: 010-0000-P78									
4 PLACE	± **	±. **		APPD: Linson曾偉雄 2019/12/02											
3 PLACE	± **	±. **		CHKD: Linson曾偉雄 2019/12/02		010-0000-P78									
2 PLACE	± 0.20	±. **		DRAW:											
1 PLACE	± 0.30	±. **		DESIGN: Lu陳惠枝 2019/11/29		 <table><tr><td>SCALE</td><td>SHEET</td><td>REV</td></tr><tr><td>1/1</td><td>1/1</td><td>B</td></tr></table>				SCALE	SHEET	REV	1/1	1/1	B
SCALE	SHEET	REV													
1/1	1/1	B													
ANGLES	X°±3°														

CONFIDENTIAL: THIS DOCUMENT CONTAINED THE INFORMATION IS PROPRIETARY AND CONFIDENTIAL TO Nextronics Engineering Corp. NO PERSON IS ALLOWED TO USE COPY, PUBLISH OR OTHERWISE DISCLOSE THE INFORMATION TO OTHERS, UNLESS BY THE PRIOR WRITTEN EXPRESS AUTHORIZATION OF Nextronics Engineering Corp. (C)COPYRIGHT- Nextronics Engineering Corp.