





| REV. | ECN NO. | REVISED | DATE |
|------|---------|---------|------|
|      |         |         |      |



工程部  
2025-05-23  
H. WANG

技术要求:  
1、截剪断面毛刺高度≤0.03mm;  
2、部件要求平整,无变形、裂纹、损伤等外观缺陷;

|     |             |      |                        |                 |
|-----|-------------|------|------------------------|-----------------|
| 1   | TERMINAL(-) | 1    | SPRING STEEL, T=0.25mm | Ni-Plating      |
| NO. | PART NAME   | Q'TY | MATERIAL               | PLATING & COLOR |

|                                       |             |                             |             |           |            |                        |  |
|---------------------------------------|-------------|-----------------------------|-------------|-----------|------------|------------------------|--|
| UNLESS OTHERWISE SPECIFIED TOLERANCES |             | MYOUNG 美阳 www.meiyangdz.com |             |           |            |                        |  |
| DECIMALS:                             | ANGLES:     | DSND                        | WangHeng    | DATE      | 2025-05-23 | TITLE:<br>7号电池弹片 负极    |  |
| X : ±0.30                             | X : ±1°     | CHKD                        | ZhouRuicai  | DATE      | 2025-05-23 |                        |  |
| X.X : ±0.25                           | X.X : ±0.5° | APVD                        | XueShunyong | DATE      | 2025-05-23 | PART NO.:<br>MY-AAA-09 |  |
| X.XX : ±0.20                          |             | WEIGHT:                     | SCALE: 1:1  | SIZE: A4  | VIEW:      |                        |  |
| X.XXX : ±0.10                         |             | SHEET 1 OF 1                | UNIT: mm    | REV.: A/0 | OBJECT: MY | DRAW NO.:MY-CP-0176    |  |