

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

A

B

C

D

E

F

G

A

B



C

D




E

F

G



3D VIEW



NOTES

- MATERIAL:
 - HOUSING: PBT ,COLOR IS BLACK;
 - CONTACT: BRASS,T=0.20±0.02mm;
 - SHELL: SPCC,T=0.3±0.02mm;
- FINISH:
 - TERMINAL:
CONTACT AREA: GOLD PLATED G/Fu";
SOLDER AREA: PLATED OVER TIN;
 - SHELL: NI PLATED OVER ALL ;
- RECINNEBDED PCB THICKNESS: 1.60mm;
- ELECTRICAL:
 - VOLTAGE RATING: 30 VAC RMS;
 - CURRENT RATING: 1.5 AMP;
 - CONTACT RESISTANCE: 30MILLIOHMS MAX.;
 - WITHSTAND VOLTAGE: 500 VAC RMS
50(60)Hz,1MIN.;
 - INSULATION RESISTANCE: 100MEGOHMS MIN
@500V DC;
- MECHANICAL:
 - MATING FORCE: 35N MAX.;
 - UNMATING FORCE: 5~35N;
 - OPERATING LIFE: 1500 CYCLES MIN.;
- ENVIRONMENTAL:
 - STORAGE TEMPERATURE RANGE: -40°C~+85°C
 - OPERATION TEMPERATURE RANGE: -25°C~+70°C;
- SALT SPRAY TEST:24H(EXCLUDING RIVETED BENDS)
- SOLDERABILITY: 245±5°C,5±0.5S

3	外壳	铁	镀镍	
2	接触	铜	镀金	
1	基座	PBT	黑色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	USB座
料 号 PART NO	HC-USB2.0-L195-02J

UNLESS OTHERWISE, GENERAL TOLERANCE:	比 列 SCALE	1:1	制 图 DRAW	
X. xxx ±0.10 X. xx ±0.20 X. x ±0.30 ANGULAR: X. xx° ±1° X. x° ±3° X. ° ±5°	单 位 UNIT	MM	审 核 CHECKED	AhYe
	张 数 PART NO	1 OF 1	批 准 APPROVE	夏操云
	版 本 REV	A		赵亮亮

