


REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	01	BATCH PRODUCTION INITIAL RELEASE.	2020.04.14	李全榮



Specifications

Current Rating:1Amp AC/DC

Voltage Rating:125V AC/DC

Contact Resistance:20mΩ Max.

Insulation Resistance:100MΩ Min.

Dielectric Withstanding Voltage:500VAC




Temperature Range:-40°C to +105°C

Materials


Contact Material:Bhosphor Bronze

Insulator Material:LCP UL 94V-0

All materials must meet GREENCONN hazardous substances control standards.



CIRCUITS	DIM A	DIM B
02	4.25	1.25
03	5.50	2.50
04	6.75	3.75
05	8.00	5.00
06	9.25	6.25
07	10.50	7.50
08	11.75	8.75
09	13.00	10.00
10	14.25	11.25
11	15.50	12.50
12	16.75	13.75
13	18.00	15.00
14	19.25	16.25
15	20.50	17.50



Ordering Information

G WDC102 - XX XX A 012 C X S X-9B

No. of Pins per Row 02~15 Standard Plating 01=Tin Color 2=White Standard Packing F=CAP+Tape&Reel

PCB ALYOUT(±0.05)

格稜股份有限公司 Greenconn Corporation					GENERAL TOLERANCE		DESIGNED: 李全榮	DATE: 2020.04.14	DWG. NO.	TITLE. 1.25mm pitch Wafer
					X.±	X.±	CHECKED: 方秋香	DATE: 2020.04.14	GWDC102-CA12CS	
					.X.±	.X±0.25	APPROVED: 方秋香	DATE: 2020.04.14	PART NO.	
					.XX.±	.XX±0.15			GWDC102-XXXXA012CX SX-9B	
REV.	UNIT.	SCALE.	PAGE.		.XXX.±	.XXX±0.10				
01	mm	1:1	1/1							