


A	—
B	—
C	—
D	—
E	—
F	—
G	—
H	



Technical drawing of the 10-pin connector showing two views: a perspective view and a side view with dimensions.

Perspective View: Shows the connector from an isometric perspective. It features a rectangular body with a latch on the side and a 10-pin connector on the front. The top surface has four mounting holes. The side view shows a latch mechanism and a small rectangular label with the number '10'.

Side View with Dimensions: Shows the connector from the side, highlighting the cable connection area and the latch mechanism. The dimensions are as follows:

- Overall Width:** 6.65
- Pin Array Width:** 1.15
- Pin Array Height:** 1.14
- Pin Array Spacing:** 3.95
- Pin Array Depth:** 3.40
- Pin Array Label:** CABLE
- Pin Array Label Position:** 6.50 MAX

GENERAL TOLERANCE	
.X:= ± 0.30	.X*:= $\pm 2^\circ$
.XX:= ± 0.25	.XX*:= $\pm 1^\circ$
.XXX:= ± 0.15	.XXX*:= $\pm 0.5^\circ$
UNIT: MM	PROJECTION:
SCALE: 1:1	
SHEET: 1/1	

DESCRIPTION: 板上DIP+SMT CL3.40 PH4.0 外壳脚长2.40		
PART NO:	USB30-AF-025	REV: 1.0
OLD CODE:	USBC1-AF-025	
DRAWING NO:		SIZE: A4