




N=PIN数



P.C.B LAYOUT



Material 材料

Insulator 塑胶: PBT (UL 94V-0)

Contact 端子: Brass 黄铜

Surface Coating 表面镀层: Gold Over Nickel 里镍外金

Electrical Characteristics 电气特性

Current rating 额定电流: 2.5Amps

Dielectric Withstanding Voltage 耐压:

AC 500V for 1 Minute.

Insulator Resistance 绝缘电阻: 1000MΩ Min.

Contact Resistance 接触电阻: 20mΩ Max.

Operating Temperature 工作温度: -40℃ ~ +105℃

Max. Processing Temp 瞬时温度:

PBT 230° C ± 5° 10s

未注尺寸公差			PZ2.54-1*N-fwz		上海洲日电子有限公司						
尺寸	公差				Shanghai Zhouri Electronics CO.,LTD						
	长度	角度			上海康司玛电子设备进出口有限公司						
	X.	±0.3			±5°	Shanghai KangSiMa Eletronic Equipment					
	X.X	±0.2			±3°	import and export Co.,LTD					
X.XX	±0.15		版本编号	20171018 A/1		TEL:86-21-34975176/51571121					
制图	周元金	201171018	图纸编号	ZR20171018-258-1							
审核	张海娜	201171018	物料编号			1:1		mm		图幅	A4
核准	章妹	201171018	第三视角			1		1			