


SPECIFICATION

1. Rating : DC 30V 0.5A;
2. Contact resistance: $\leq 30m\Omega$;
3. Insulation resistance: $\geq 100M\Omega$ (DC250V);
4. Withstand voltage: 500VAC ;
5. Insertion and extraction force: 3-30N;
6. life test: 5,000 cycles;
7. Operation temperature range: $-20^{\circ}C \sim 70^{\circ}C$;
8. Preservative temperature range: $-40^{\circ}C \sim 85^{\circ}C$;
9. Sign "▲" is importance dimension.

电话 : 0769-82310511-867
 邮箱 : hooya89@hooya.hk
 V : hooya89

PIN	Ø2.0	Ø2.35	Ø2.5	Ø3.0	Ø3.2
-----	------	-------	------	------	------

					TOLERANCE UNLESS SPECIFIED					
6	Shunt terminal	3	Brass	1	Tin plating	UP TO 5mm: ± 0.1	ANGULAR	A0		
5	Tip spring	2	Phosphor bronze	1	Tin plating	ABOVE 5mm: ± 0.2	$\pm 1^{\circ}$	NO	DATE	REVISIONS
4	Center pin terminal	1	Brass	1	Tin plating	TITLE: DC JACK		UNIT : MM	ROHS COMPLIANT	DWN
3	Center pin	1	Brass	1	Nickel plating	MODEL: DC-063-2.5-01		SCALE: 4:1	CHK'D	
2	Cover	1	PBT			DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司		APPD		
1	Housing	1	PBT					PRO.AGL:		REV : A0
NO.	PART	NAME	MATERIAL	QTY	FINISHING					