



R

Circuit Diagram

NO.1



PART NO | T (无柱)



NO.2

PART NO	H
A	4.3
C	5

NO.3

NO.3	VIGOR
3	180±50
4	250±50
5	350±50

NO.4

PART NO	MATERIAL/QTY
S	SUS/1PCS
D	SUS/2PCS

NO.5

PART NO	L	L1
A	8	10
B	8.5	11
C	9	11
D	9.5	12
E	10	12

NO.6-NO.7

PART NO	NOTE
01~99	SERIAL NUMBER

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL		FINISHING	REMARK
				Brass(0.30t)	Plating silver		
⑤	Terminal	—	2	Brass(0.30t)	Plating silver	—	—
④	Contact	—	1	F.Ag/SUS	—	—	—
③	Base	—	1	PA46	WHITE	—	—
②	Cover	—	1	SPCC	Plating Nickel	—	—
①	Keystoke	—	1	PA46	WHITE	—	—

APPROVALS		DATE	TITLE:	TACT SWITCHS	
DRAWN	J.X.Zhang	2013/5/30		PART NO.	K2-1101S□-□□□□-□□
CHECKED					
APPROVALS					

TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
	10~30	±0.20				
	5~10	±0.15				
	~ 5	±0.10	±2°	DRAWING NO.		SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.

hro®