

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.9.28	阿树

PART NO.:

X2026 W R-2xXX D-46 SN XX
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

■ SPECIFICATIONS

- Voltage rating: 250V AC/DC
- Current rating: 3A AC/DC
- Withstanding Voltage: 1000V AC/minute
- Temperature range: -40°C ~ +125°C
- Insulation resistance: ≥ 1000MΩ
- Contact resistance: ≤ 30mΩ
- After environmental testing: ≤ 50mΩ

- ① Series No
② Category: W-Wafer
③ Welding Board Angle: R-Straight 90°
④ Row No. Pin No: 2xXX-2x02~2x30Pin
⑤ Plug the Pin&Special NO:
D-With Lock In the middle
⑥ Material: 46-PA46 94V-0; 4T-PA4T 94V-0
⑦ Plating Category: SN-Bright Tin Plating
V03-Gold 3u"
⑧ Color: Blank-Natural Color

poles	Dimensions(mm)			poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2x02	2.00	6.00	4.90	2x10	18.00	22.00	20.90	2x18	34.00	38.00	36.90
2x03	4.00	8.00	6.90	2x11	20.00	24.00	22.90	2x19	36.00	40.00	38.90
2x04	6.00	10.00	8.90	2x12	22.00	26.00	24.90	2x20	38.00	42.00	40.90
2x05	8.00	12.00	10.90	2x13	24.00	28.00	26.90	2x30	58.00	62.00	60.90
2x06	10.00	14.00	12.90	2x14	26.00	30.00	28.90				
2x07	12.00	16.00	14.90	2x15	28.00	32.00	30.90				
2x08	14.00	18.00	16.90	2x16	30.00	34.00	32.90				
2x09	16.00	20.00	18.90	2x17	32.00	36.00	34.90				

X2026WR-2xXXD-46V03	PA46 UL 94V-0	Brass	Gold 3u"	X2026H-D
X2026WR-2xXXD-4TSN	PA4T UL 94V-0		Tin-Plated	
X2026WR-2xXXD-46SN	PA46 UL 94V-0			
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	2.00mm Crimp Style Connector
CHECKED		UNIT:	mm/in	PART NO.:	X2026WR-2xXXD-XXXXX
APPROVED		SIZE:	A4	DWG NO.:	

