



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES

MATERIAL

- 1.HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.
- 2.CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
- 3.PLATING: SELECT GOLD PLATING OVER NICKEL 50u".
- 4.SHIELD: BRASS T0.20mm 40u" NICKEL PLATED.

ELECTRICAL



- 1.VOLTAGE RATING: 125 VAC RMS.
- 2.CURRENT RATING: 1.5 AMP.
- 3.CONTACT RESISTANCE: 40 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
- 5.DIELECTRIC DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL


- 1.DURRABILITY: 750 CYCLES MIN.
- 2.MATING/UNMATING FORC: 2.24 KG.F MAX.

ENVIRONMENTAL:


- 1.STORAGE: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.OPERATION: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.



焊脚尺寸以顺畅过孔规为准



8	—
7	—
6	RX-
5	—
4	—
3	RX+
2	TX-
1	TX+
PIN	说明



PCBLAYOUT T=1.6mm
TOL:±0.05

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.35	X':±3"	PART NO. RJ45-2005-8P	TITLE: RJ45 56 B型无弹无灯DIP		
X.X:±0.25	X.X':±2"				
X.XX:±0.15	X.XX':±1"				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/1