








说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 5.满足灼热丝温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:3A AC/DC
- 8.额定电压:250V AC/DC
- 9.接触阻抗:10mΩ Max.
- 10.绝缘阻抗:1000MΩ Min.
- 11.耐电压:1000V AC FOR 1 MINUTE

P/N	PIN	DIM A	DIM B	DIM C
BX-HA2.54-2PWT-XM	2	2.50	9.90	5.90
BX-HA2.54-3PWT-XM	3	5.00	12.40	8.40
BX-HA2.54-4PWT-XM	4	7.50	14.90	10.90
BX-HA2.54-5PWT-XM	5	10.00	17.40	13.40
BX-HA2.54-6PWT-XM	6	12.50	19.90	15.90
BX-HA2.54-7PWT-XM	7	15.00	22.40	18.40
BX-HA2.54-8PWT-XM	8	17.50	24.90	20.90
BX-HA2.54-9PWT-XM	9	20.00	27.40	23.40
BX-HA2.54-10PWT-XM	10	22.50	29.90	25.90
BX-HA2.54-11PWT-XM	11	25.00	32.40	28.40
BX-HA2.54-12PWT-XM	12	27.50	34.90	30.90
BX-HA2.54-13PWT-XM	13	30.00	37.40	33.40
BX-HA2.54-14PWT-XM	14	32.50	39.90	35.90
BX-HA2.54-15PWT-XM	15	35.00	42.40	38.40
BX-HA2.54-16PWT-XM	16	37.50	44.90	40.90
BX-HA2.54-17PWT-XM	17	40.00	47.40	43.40
BX-HA2.54-18PWT-XM	18	42.50	49.90	45.90
BX-HA2.54-19PWT-XM	19	45.00	52.40	48.40
BX-HA2.54-20PWT-XM	20	47.50	54.90	50.90

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-HA2.54-NPWT-XM	版本 REV.	A
			X.±0.30	X°.±5°	审核 CHECK	EVA			品名 TITLE	HA-SMT-AW带扣针座	页次 SHEET	1/1
			.X±0.25	X.X°.±3°	核准 APPROVAL	JADE			客户料号 CUTM.NO.			
			.XX±0.20	X.XX°.±1°	单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)			