


Data Sheet

V 1.3 / Feb. 2024

MSM381ACBA01

Analog output MEMS microphone



MSM381ACBA01

Analog output MEMS microphone



CONTENTS:

1. Title	1
2. Catalogue	2
3. General Description	3
4. Features	3
5. Applications	3
6. Product View.....	3
7. Absolute Maximum Ratings	4
8. Acoustic & Electrical Specifications.....	4
9. Typical Frequency Response	5
10. Outline Dimensions & Pin Definition	6
11. Reliability Specifications	7
12. Packaging & Marking Detail	8
13. Recommend Reflow Profile	9
14. Recommended Interface Circuit	10
15. Additional Notes	11
16. Storage and Transportation	11
17. Materials Statement	11
18. Revision History	12

MSM381ACBA01

Analog output MEMS microphone



GENERAL DESCRIPTION

MSM381ACBA01 is an omnidirectional, Bottom-port, analog output MEMS microphone. It has high performance and reliability. It is with enhanced RF immunity performance .

MSM381ACBA01 is available in a thin 2.75 mm × 1.85 mm × 0.90 mm metal can LGA package. It is SMT compatible with no sensitivity degradation.


APPLICATIONS

- ✧ Mobile Phone
- ✧ Laptop
- ✧ Tablet computer
- ✧ Bluetooth headset
- ✧ Earphone
- ✧ Wearable intelligent equipment

FEATURES

- ✧ High AOP
- ✧ Omnidirectional
- ✧ Excellent RF immunity
- ✧ Standard SMD Reflow
- ✧ Compatible with Sn/Pb and Pb-free solder processes
- ✧ RoHS/Halogen free compliant
- ✧ Sensitivity Matching within +/-1dB

PRODUCT VIEW



MSM381ACBA01

Analog output MEMS microphone



ABSOLUTE MAXIMUM RATINGS

Parameter	Maximum value	Unit
Supply Voltage	-0.3 to 4.2	V
Sound Pressure Level	140	dB SPL
Storage temperature	-40 to 125	°C

Stresses exceeding these “Absolute Maximum Ratings” may cause permanent damage to the device. These are stress ratings only. Functional operation at these or any other conditions beyond those indicated under “Acoustic & Electrical Specifications” is not implied. Exposure beyond those indicated under “Acoustic & Electrical Specifications” for extended periods may affect device reliability.

ACOUSTIC & ELECTRICAL SPECIFICATIONS


All data taken @1.8V, 25 ± 10°C, RH 50±20% ,unless otherwise specified					
	Limits			unit	condition
	Min.	Nom.	Max.		
Directivity	Omni directional				
Sensitivity	-39	-38	-37	dB	@1kHz ref 1V/Pa
Operation voltage	1.6	-	3.6	V	
Freq. range	Refer to the frequency response graphic			Hz	Ref to sensitivity@1kHz
Sensitivity loss across supply voltage	No change across the voltage range			dB	
Signal to noise ratio	-	63.5	-	dB	94dB SPL @1kHz, A-weighted
THD	-	0.1	0.5	%	94dB SPL @1kHz S =Nom, Rload > 2 k
AOP	-	128	-	dB SPL	10% THD @1kHz S =Nom, Rload > 2 k
Polarity	Increasing output voltage				Increasing sound pressure
Output impedance	-	400	-	Ω	@1kHz
DC Output	1.1			V	
PSRR	-	70	-	dB	200mVpp sine wave @ 1 kHz, V _{DD} = 1.8V
PSR	-	-100	-	dBV(A)	100 mVpp square wave@ 217 Hz, V _{DD} = 1.8V, A-weighted
Current consumption	-	150	170	μA	

MSM381ACBA01

Analog output MEMS microphone



TYPICAL FREQUENCY RESPONSE





MSM381ACBA01

Analog output MEMS microphone



OUTLINE DIMENSIONS AND PIN DEFINITION:



TOP VIEW

SIDE VIEW

BOTTOM VIEW

PIN function description

PIN#	Function
1	VDD
2	OUT
3	GND

Item	Dimension	Tolerance
Length (L)	2.75	± 0.10
Width (W)	1.85	± 0.10
Height (H)	0.90	± 0.10
Acoustic Port (AP)	$\varnothing 0.25$	± 0.05

Dimensions are in millimeters, tolerance is $\pm 0.15\text{mm}$ unless otherwise specified.

MYWW XXXX	M	Memsensing
	Y	Year(A~Z)
	WW	Week
	XXXX	Serial Number

MSM381ACBA01

Analog output MEMS microphone



RELIABILITY SPECIFICATIONS

Test	Description
Thermal Shock	100 cycles air-to-air thermal shock from -40°C to +125°C with 15 minute soaks. (IEC68-2-4)
High Temperature Storage	1,000 hours at +105°C environment. (IEC68-2-2 Test Ba)
Low Temperature Storage	1,000 hours at -40°C environment. (IEC68-2-2 Test Aa)
Reflow	5 reflow cycles with peak temperature of +260°C.
ESD-HBM	3 discharges of ± 2 kV direct contact to I/O pins. (IEC 61000-4-2)
ESD- LID-GND	3 discharges of ± 8 kV direct contact to lid while unit is grounded. (IEC 61000-4-2)
ESD-MM	3 discharges of ± 200 V direct contact to I/O pins. (IEC STM5.2)
Vibration	4 cycles of 20 to 2,000 Hz sinusoidal sweep with 20 G peak acceleration lasting 12 minutes in X, Y and Z directions. (Mil-Std-883E, Method 2007.2.A)
Mechanical Shock	3 pulses of 10,000 G in the X, Y and Z direction. (IEC68-2-27 Test Ea)
High Temperature Bias	1,000 hours at +105°C under bias (IEC68-2-2 Test Ba)
Low Temperature Bias	1,000 hours at -40°C under bias (IEC68-2-2 Test Aa)
Temperature/Humidity Bias	1,000 hours at +85°C/85% R.H. under bias. (JESD22-A101A-B)
Drop Test	To be no interference in operation after dropped to 1.0cm steel plate 18 times from 1.5 meter height






NOTE: Sensitivity should vary within ± 3 dB from initial sensitivity. (The measurement to be done after 2 hours of conditioning at $25 \pm 10^\circ\text{C}$, $50 \pm 20\%$ R.H.)

MSM381ACBA01

Analog output MEMS microphone



PACKAGING & MARKING DETAIL:



ITEM	W	E	F	ØD0	K0
DIM(mm)	12.00±0.30	1.75±0.10	5.50±0.10	1.50 ^{+0.10} ₀	1.35±0.10
ITEM	P0	10P0	P1	A0	B0
DIM(mm)	4.00±0.10	40.00±0.20	8.00±0.10	3.05±0.10	2.15±0.10
ITEM	P2	T			
DIM(mm)	2.00±0.10	0.25±0.05			

Note:

- 1) Dimensions are in mm;
- 2) Don't put the vacuum suction nozzle alignment the port hole;
- 3) Tape & Reel Per EIA-481 standard;
- 4) Label applied to external package and directly on reel;
- 5) Static voltage <100V;


Model Number	Reel Diameter	Quantity Per Reel
MSM381ACBA01	13 inch	5700

MSM381ACBA01

Analog output MEMS microphone



RECOMMEND REFLOW PROFILE:



Description	Parameter	Pb-free
Average ramp-up rate	T_{smax} to T_P	3°C/sec max
Preheat		
Minimum temperature	T_{SMIN}	150 °C
Maximum temperature	T_{SMAX}	200 °C
Time(T_{SMIN} to T_{SMAX})	t_s	60 sec to 180 sec
Ramp-up rate	T_{SMAX} to T_L	1.5 ~ 2°C/sec
Time maintained above liquidus temperature	t_L	60 sec to 150 sec
Liquidus temperature	T_L	217 °C
Peak temperature	T_P	260 °C
Time within 5°C of actual peak temperature	t_p	20 sec to 40 sec
Ramp-down rate	T_P to T_{smax}	6 °C/sec max
Time 25 °C ($t_{25\text{ °C}}$) to peak temperature	t	8 minutes max

NOTE: When MEMS MIC is soldered on PCB, the reflow profile is set according to solder paste and the thickness of PCB etc.


MSM381ACBA01

Analog output MEMS microphone



RECOMMENDED INTERFACE CIRCUIT:

- Recommended Application Example (differential amplification circuit)



NOTE: It is recommended that the components on the left side of red line be placed close to MIC, and components on the right side of red line be placed close to codec.

MSM381ACBA01

Analog output MEMS microphone



ADDITIONAL NOTES

- (A) MSL (moisture sensitivity level) Class 1.
- (B) Maximum of 3 reflow cycles is recommended.
- (C) In order to minimize device damage:
 - Do not board wash or clean after the reflow process.
 - Do not brush board with or without solvents after the reflow process.
 - Do not directly expose to ultrasonic processing, welding, or cleaning.
 - Do not insert any object in port hole of device at any time.
 - Do not apply air pressure into the port hole.
 - Do not pull a vacuum over port hole of the microphone.
 - Do not apply a vacuum when repacking into sealed bags at a rate faster than 0.5 atm/sec.

STORAGE AND TRANSPORTATION

- (A) Keep MEMS MIC in warehouse with less than 75% humidity and without sudden temperature change, acid air, any other harmful air or strong magnetic field.
 - Recommend floor life (out of bag) at factory no more than 4 weeks.
- (B) The MEMS MIC with normal pack can be transported by ordinary conveyances. Please protect products against moist, shock, sunburn and pressure during transportation.

MATERIALS STATEMENT

Meet the requirements of MEMSensing standard on hazard substances control (including RoHS2.0+REACH+Halogen-Free, etc.), with “HSF” identification on label.

MSM381ACBA01

Analog output MEMS microphone



REVISION HISTORY:

Revision	Subjects (major changes since last revision)	Date
1.0	Initial Release	2023-11-22
1.1	Update Acoustic & Electrical Specifications	2023-12-28
1.2	Update Acoustic & Electrical Specifications	2024-01-19
1.3	Update Acoustic & Electrical Specifications	2024-02-29

公司销售、技术支持联系方式

(<http://www.memsensing.com>)

For English:

MEMSensing Microsystems(Suzhou,China)
Co., Ltd.

No. 8, Wangjiabang Lane, Suzhou Industrial
Park, China (Jiangsu) Pilot Free Trade Zone,
Suzhou 215123

Phone: +86 512 62956055

Fax: +86 512 62956056

中文用户:

苏州敏芯微电子技术股份有限公司

中国（江苏）自由贸易试验区苏州片区苏州工业园
区旺家浜巷 8 号 215123

电话: +86 512 62956055

传真: +86 512 62956056

Disclaimer: specifications and characteristics are subject to change without notice. MEMSensing Microsystems Co., Ltd. assumes no liability to any customer, licensee or any third party for any damages or any kind of nature whatsoever related to using this technical data.