








3D View

STATED AT COMPRESSION
(FOR REFERENCE ONLY)

NOTES

- (1) MATERIAL: Y-CUT-FX-EH THICKNESS=0.08mm
- (2) PRODUCT SPECIFICATIONS:
 - 2-1: RATED CURRENT: 1.0A
 - 2-2: VOLTAGE RATING: 12.0V
 - 2-3: CONTACT RESISTANCE: 30mΩ/MAX
 - 2-4: WELDING THRUST: ≥ 3KG
 - 2-5: OPERATING TEMPERATURE: -40°C~+85°C
 - 2-6: DURABILITY: 20000 CYCLES
- (3): SALT SPRAY: 48 HOURS
- (4): ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 60~120u"
- (5): SWEAT TEST:
 - 5-1: ≤5 CYCLE: NO CORROSION NORMAL CHARGING FUNCTION AND PERFORMANCE
 - 5-2: 6~30 CYCLE: CO CORROSION IS ALLOWED, CHARGING FUNCTION AND PERFORMANCE ARE NOEMAL
- (6): REQUIREMENTS
 - 6-1: TERMINAL TO EAT FULL TIN, NOT PEELING WELDING OBVIOUS COLOR AND OTHER ADVERSE
 - 6-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS

RECOMMENDED PCB LAYOUT
TOLERANCE ±0.05 (焊盘推荐图)

SCALE 2/1



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X" ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 天线弹片 L2. 50*W1. 14*H4. 20
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-TXT2511442A
UNIT: mm [inch] SCALE: 1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2412200939
			SHEET NO. 1 OF 1