







3D View



- NOTES:
- 1:MATERIAL  
1-1: SUS-301 THICKNE=0.10MM
  - 2:SPECIFICATIONS  
2-1: RATED CURRENT: 1.0A  
2-2: VOLTAGE RATING: 1.5V  
2-3: CONTACT RESISTANCE: 80mΩ/MAX  
2-4: WELDING THRUST: ≥3KG  
2-5: OPERATING TEMPERATURE: -40°C~+85°C
  - 3:DURABILITY: 1500 CYCLES
  - 4:SALT SPRAY TIME: 24H
  - 5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN
  - 6:REQUIREMENTS  
6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,  
WELDING OBVIOUS COLOR AND OTHED ADVERSE  
6-2:ROHS、REACH、HF HALOGER ADVERSE OF DOMESTIC  
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS



RECOMMENDED PCB LAYOUT  
TOLERANCE:±0.05MM  
(FOR REFERENCE ONLY)



METAL MASK T=0.08  
TOLERANCE:±0.05MM  
(FOR REFERENCE ONLY)



深圳市华宇创精密电子有限公司

|                                                                            |                    |                      |                                        |                 |
|----------------------------------------------------------------------------|--------------------|----------------------|----------------------------------------|-----------------|
| TOLERANCE:<br>X.X ±0.30<br>X.XX ±0.25<br>X.XXX ±0.15<br>X.' ±2' X.X' ±0.5' | DRAWN BY :<br>陈一鸣  | DATE :<br>2014-02-23 | PART NAME:<br>天线弹片 L2. 50*W1. 0*H1. 50 |                 |
|                                                                            | CHECKED BY:<br>马跃  | DATE :<br>2014-02-23 | PART NO.<br>MOLD NO.                   | HYCW-TXT251015A |
| UNIT: mm [inch]<br>SCALE:1:1 SIZE: A4                                      | APPROVED BY:<br>邱敏 | DATE :<br>2014-02-23 | DRAW NO:                               | HYC-2412301207  |
|                                                                            |                    |                      | SHEET NO.                              | 1 OF 1          |