

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.11.8	阿树

A

B

C



D

A

B

C

D



- SPECIFICATIONS
- Voltage rating: 250V AC/DC
 - Current rating: 3A AC/DC
 - Withstanding Voltage: 1500V AC/minute
 - Temperature range: -40°C ~ +125°C
 - Insulation resistance: $\geq 1000M\Omega$
 - Contact resistance: $\leq 20m\Omega$
 - After environmental testing: $\leq 30m\Omega$

PART NO.:

X9555 W R-2xXX E-PT XX XX
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No
② Category: W-Wafer
③ Welding Board Angle: R-Stright 90°
④ Row No. Pin No: 2xXX-02~20Pin
⑤ Special NO: E-matching 9555H-2xXXE HSG,
K the feet, DIP=2.90mm 1-K the feet, DIP=2.50mm
⑥ Material: PT-PBT 94V-0
⑦ Plating Category: SN-Bright Tin Plating 70u"
V01-Gold Flash
⑧ Color: Blank-Natural Color

poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C
2x03	5.09	10.12	8.12	2x12	27.94	32.98	30.98
2x04	7.62	12.66	10.66	2x13	30.48	35.52	33.52
2x05	10.16	15.20	13.20	2x14	33.02	38.06	36.06
2x06	12.70	17.74	15.74	2x15	35.56	40.60	38.60
2x07	15.24	20.28	18.28	2x16	38.10	43.14	41.14
2x08	17.78	22.82	20.82	2x17	40.64	45.68	43.68
2x09	20.32	25.36	23.36	2x18	43.18	48.22	46.22
2x10	22.86	27.90	25.90	2x19	45.72	50.76	48.76
2x11	25.40	30.44	28.44	2x20	48.26	53.30	51.30

X9555WR-2xXXEX-PTV01	PA9T UL 94V-0	Brass	Gold-Flash	X9555H-E
X9555WR-2xXXEX-PTSN			Tin-Plated	
PART NO	Material	Finish(Pin)	Finish(Pin)	Suitable XKBTerminal

Dim"L"	E1	2.50
	E	2.90

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE:	2.54mm Crimp Style Connectors
PART NO.:	X9555WR-2xXXE-PTXX
DWG NO.:	