







(0.06)WORKING HEIGHT




## NOTES


- (1) MATERIAL: SUS-301 THICKNESS=0.08mm
- (2) PRODUCT SPECIFICATIONS:
  - 2-1: RATED CURRENT: 2.0A
  - 2-2: VOLTAGE RATING: 10.0V
  - 2-3: CONTACT RESISTANCE: 50mΩ/MAX
  - 2-4: WELDING THRUST: ≥ 3KG
  - 2-5: OPERATING TEMPERATURE: -40°C~+85°C
  - 2-6: DURABILITY: 1500 CYCLES
- (3): SALT SPRAY: 24 HOURS
- (4): FINISH: 50μm MIN NICKEL UNDERPLATING OVER ALL.
- (5): REQUIREMENTS
  - 5-1: TERMINAL TO EAT FULL TIN, NOT PEELING WELDING OBVIOUS COLOR AND OTHER ADVERSE
  - 5-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS



RECOMMENDED PCB LAYOUT  
TOLERANCE±0.05(焊盘推荐图)



METAL MASK T=0.10  
TOLERANCE±0.05(钢网推荐图)



深圳市华宇创精密电子有限公司

|                                                                           |                    |                      |                                    |                 |
|---------------------------------------------------------------------------|--------------------|----------------------|------------------------------------|-----------------|
| TOLERANCE:<br>X.X ±0.30<br>X.XX ±0.25<br>X.XXX ±0.15<br>X' ±2" X.X' ±0.5" | DRAWN BY :<br>陈一鸣  | DATE :<br>2014-02-23 | PART NAME:<br>天线弹片 L1.90*W1.0*H1.4 |                 |
|                                                                           | CHECKED BY:<br>马跃  | DATE :<br>2014-02-23 | PART NO.                           | HYCW-TXT191014A |
| UNIT: mm [inch]<br>SCALE:1:1 SIZE: A4                                     | APPROVED BY:<br>邱敏 | DATE :<br>2014-02-23 | DRAW NO:                           | HYC-2509090956  |
|                                                                           |                    |                      | SHEET NO.                          | 1 OF 1          |