



PJM100P40DN

P-Channel Enhancement Mode Power MOSFET

Product Summary

- $V_{DS} = -40V, I_D = -100A$
- $R_{DS(on)} < 8m\Omega @ V_{GS} = -10V$
- $R_{DS(on)} < 11m\Omega @ V_{GS} = -4.5V$


Features

- Advanced Trench Technology
- 100% Avalanche Tested
- RoHS Compliant
- Halogen and Antimony Free
- Moisture Sensitivity Level 3


Application

- Load Switch
- PWM Application
- Power Management

Marking Code




PDFN5x6-8L



Pin	Description
1,2,3	Source
4	Gate
5,6,7,8	Drain

Schematic Diagram



Absolute Maximum Ratings

Ratings at 25°C case temperature unless otherwise specified.

Parameter	Symbol	Value	Unit
Drain-Source Voltage	$-V_{DS}$	40	V
Gate-Source Voltage	V_{GS}	± 20	V
Drain Current-Continuous	$-I_D$	100	A
Drain Current-Pulsed ^{Note1}	$-I_{DM}$	328	A
Maximum Power Dissipation	P_D	58	W
Junction Temperature	T_J	150	°C
Storage Temperature Range	T_{STG}	-55 to +150	°C

Thermal Characteristics

Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	2.16	°C/W
--------------------------------------	-----------------	------	------



PJM100P40DN

P-Channel Enhancement Mode Power MOSFET

Electrical Characteristics

(T_J=25°C unless otherwise specified)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	-V _{(BR)DSS}	V _{GS} =0V, I _D =-250μA	40	--	--	V
Zero Gate Voltage Drain Current	-I _{DSS}	V _{DS} =-40V, V _{GS} =0V	--	--	1	μA
Gate-Body Leakage Current	I _{GSS}	V _{GS} =±20V, V _{DS} =0V	--	--	±100	nA
Gate Threshold Voltage ^{Note2}	-V _{GS(th)}	V _{DS} =V _{GS} , I _D =-250μA	1	--	2.5	V
Drain-Source On-Resistance ^{Note2}	R _{DS(on)}	V _{GS} =-10V, I _D =-20A	--	--	8	mΩ
		V _{GS} =-4.5V, I _D =-20A	--	--	11	mΩ
Forward Transconductance	g _{FS}	V _{DS} =-5V, I _D =-10A	--	63	--	S
Dynamic Characteristics						
Input Capacitance	C _{iss}	V _{DS} =-20V, V _{GS} =0V, f=1MHz	--	6638	--	pF
Output Capacitance	C _{oss}		--	545	--	pF
Reverse Transfer Capacitance	C _{rss}		--	345	--	pF
Gate Resistance	R _g	V _{DS} =0V, V _{GS} =0V, f=1MHz	--	2.2	--	Ω
Total Gate Charge	Q _g	V _{DS} =-20V, I _D =-20A, V _{GS} =-10V	--	118	--	nC
Gate-Source Charge	Q _{gs}		--	13	--	nC
Gate-Drain Charge	Q _{gd}		--	22	--	nC
Switching Characteristics						
Turn-on Delay Time	t _{d(on)}	V _{DD} =-20V, I _D =-20A, V _{GS} =-10V, R _{GEN} =3Ω	--	16	--	nS
Turn-on Rise Time	t _r		--	17	--	nS
Turn-off Delay Time	t _{d(off)}		--	68	--	nS
Turn-off Fall Time	t _f		--	31	--	nS
Source-Drain Diode Characteristics						
Diode Forward Voltage ^{Note2}	-V _{SD}	V _{GS} =0V, I _S =-20A	--	--	1.2	V
Diode Forward Current	-I _S		--	--	100	A

Note: 1. Repetitive Rating: Pulse width limited by maximum junction temperature.







2. Pulse Test: Pulse width≤300μs, duty cycle≤2%.



PJM100P40DN

P-Channel Enhancement Mode Power MOSFET




Typical Characteristic Curves





PJM100P40DN

P-Channel Enhancement Mode Power MOSFET






PJM100P40DN

P-Channel Enhancement Mode Power MOSFET


Package Outline

PDFN5x6-8L


Dimensions in mm




TOP VIEW



RIGHT VIEW



BOTTOM VIEW



SIDE VIEW