

REV	ECN No.	DATE	REMARK
A	NEW	2020.05.22	NEW RELEASE
B	---	2023.06.14	增加绿色规格
C	---	2023.12.26	修改厚度3.78与实物3.65相符














TABLE:				
7	CAP	1PCS	LCP UL94V-0	BALCK
6	SPRING	1PCS	SUS 301 T=0.4	SPRING卡勾: SUS301;T=0.4, 半雾锡
5	TERMINAL	24PCS	C7025 T=0.15	镍底50-150U, 锡100-200U, 接触点镀金
4	EMI PLATE	2PCS	SUS 304 T=0.10	清洗
3	FRONT SHELL	1PCS	SUS 316L T=0.15	电镀半光镍, 镀镍50U以上,盐雾48H
2	EMI-Molding	2PCS	LCP UL94V-0	SEE THE PART NUMBER CODE
1	TERMINAL-Molding	2PCS	LCP UL94V-0	BALCK
No.	NAME	Q'TY	MATERIAL	FINISH
GENERAL TOLERANCES (UNLESS SPECIFIED)			DRAWN BY: HuangXiaoHao	Date: 2023.12.26
X.XXX	±0.10	CHECKED BY: liuzongliang		Date: 2023.12.26
X.XX	±0.20	APPROVED BY: Jacky		Date: 2023.12.26
X.X	±0.30	THIRD ANGLE PROJECTION		
ANGULAR	±3°	UNT	SCALE	
		mm	1:1	
DRAWING		A4	SHEET NO.	1 OF 3
PART NO.		CM090-24LB02U-02	DWG NO.	CM090-24-02
TITLE		USB TYPE-C M 24Pin WHIT EMI		
REV.		C		




REV	ECN No.	DATE	REMARK
A	NEW	2020.05.22	NEW RELEASE
B	---	2023.06.14	增加绿色规格
C	---	2023.12.26	修改厚度3.78与实物3.65相符



20管/扎（1000PCS）



12扎/箱（12KPCS）



	TUBE	CARTON
CONNECTOR (PCS)	50	12000

备注：
1.胶管1SET.
2.每管装成品50Pcs;
每20管一扎，并用透明胶膜将每扎紧捆；
3.每箱装12扎(12K);尾数箱用填充物填满；
4.外箱尺寸与规格印刷：详见包材图面；
5.外箱用透明胶纸带封"工"字型；
6.依外箱图示位置粘贴好产品标签
(若客户另有贴标签要求，则按其定单注明之要求贴)

GENERAL TOLERANCES (UNLESS SPECIFIED)		DRAWN BY: HuangXiaoHao	Date: 2023.12.26	ZDT 深圳市中科兴达科技有限公司 Shenzhen Zhongke Xingda Technological Co.,Ltd.	
X.XXX	±0.10	CHECKED BY:	Date:	TITLE	
X.XX	±0.25	liuzongliang	2023.12.26	USB TYPE-C M 24Pin WHIT EMI	
X.X	±0.30	APPROVED BY:	Date:	PART NO.	DWG NO.
ANGULAR	±3°	Jacky	2023.12.26	CM090-24LB02U-02	CM090-24-02
THIRD ANGLE PROJECTION	mm	UNT	SCALE	DRAWING	SHEET NO.
			1:1	A4	3 OF 3
					REV. C