





MECHANICAL:



SUGGESTED PCB LAYOUT
(TOP VIEW)



东莞市祥星电子有限公司
工程专用章

Metal Shell :Copper Alloy, Finish: 30u" Nickel
Housing :Thermoplastic,PBT,UL 94V-0,Black
Insert :Thermoplastic,PBT,UL 94V-0,Black
Contact Terminal/phosphor Bronze
6u" Gold on Contact Area, 100u" Tin on Solder,
Both over 50u" Nickel Under-Plated
Terminal/Copper Alloy T=0.35mm Thickness

Meets or exceeds IEEE 802.3 standard for 10/100/1000 Base-TX
350uH minimum OCL with 8mA Bias current
Available with or without LEDs
Minimum 1500Vrms isolation per IEEE802.3 requirement
Operating temperature -40°C to +85°C
Storage temperature -40°C to +85°C

LED ELECTRICAL CHARACTERISTIC



Standard LED	Wavelength	Forward V (Min/Max)	Forward A	Type
Green	568nm	1.8V/2.8V	20mA	squareness
Yellow	585nm	1.8V/2.8V	20mA	squareness
Orange	610nm	1.8V/2.8V	20mA	squareness

未注公差
TOLERANCE UNLESS OTHERWISE SPECIFIED

E-NETTR

东莞市祥星电子有限公司

DONGGUANG XIANGXING ELECTRONICS CO., LTD

TEL:0769-86384669

FAX:0769-81813600

Http://www.e-nettr.com

xxing-guang@163.com

比例 SCALE	张数 SHEET	单位 UNIT	角法 PROJ.	纸张 SIZE	版本 REV.	设计 DESIGN	校对 CHECK	核准 APPROVAL	品号 ITEM NO.	品名 TITLE	规格 DESC.
1/2	mm	A4							GR01M1HXS012		

