


NPN Silicon Epitaxial Transistor

for switching and amplifier applications

As complementary types the PNP transistors BC856...BC860 is recommended.



1.Base 2.Emitter 3.Collector
SOT-23 Plastic Package

Absolute Maximum Ratings ($T_a = 25\text{ }^{\circ}\text{C}$)

Parameter	Symbol	Value	Units
Collector Base Voltage	BC846 V_{CBO}	80	V
	BC847, BC850 V_{CBO}	50	V
	BC848, BC849 V_{CBO}	30	V
Collector Emitter Voltage	BC846 V_{CEO}	65	V
	BC847, BC850 V_{CEO}	45	V
	BC848, BC849 V_{CEO}	30	V
Emitter Base Voltage	BC846, BC847 V_{EBO}	6	V
	BC848, BC849, BC850 V_{EBO}	5	V
Collector Current	I_C	100	mA
Peak Collector Current	I_{CM}	200	mA
Power Dissipation	P_{tot}	200	mW
Junction Temperature	T_J	150	$^{\circ}\text{C}$
Storage Temperature Range	T_S	- 65 to + 150	$^{\circ}\text{C}$

MARKING CODE

TYPE	846A	846B	846C	847A	847B	847C	848A	848B	848C	849A	849B	849C	850A	850B	850C
MARK	1A	1B	1C	1E	1F	1G	1J	1K	1L	2A	2B	2C	2E	2F	2G

Characteristics at $T_{amb} = 25\text{ }^{\circ}\text{C}$

Parameter	Symbol	Min.	Typ.	Max.	Units
DC Current Gain at $V_{CE} = 5\text{ V}$, $I_C = 2\text{ mA}$	A h_{FE} B h_{FE} C h_{FE}	110 200 420	- - -	220 450 800	- - -
Collector Emitter Saturation Voltage at $I_C = 10\text{ mA}$, $I_B = 0.5\text{ mA}$ at $I_C = 100\text{ mA}$, $I_B = 5\text{ mA}$	V_{CEsat} V_{CEsat}	- -	- -	250 600	mV mV
Base Emitter On Voltage at $I_C = 2\text{ mA}$, $V_{CE} = 5\text{ V}$ at $I_C = 10\text{ mA}$, $V_{CE} = 5\text{ V}$	$V_{BE(on)}$ $V_{BE(on)}$	- -	- -	700 720	mV mV
Collector Cutoff Current at $V_{CB} = 30\text{ V}$	I_{CBO}	-	-	15	nA
Current Gain Bandwidth Product at $V_{CE} = 5\text{ V}$, $I_C = 10\text{ mA}$, $f = 100\text{ MHz}$	f_T	-	300	-	MHz
Output Capacitance at $V_{CB} = 10\text{ V}$, $f = 1\text{ MHz}$	C_{ob}	-	-	6	pF
Input Capacitance at $V_{EB} = 0.5\text{ V}$, $f = 1\text{ MHz}$	C_{ib}	-	9	-	pF
Noise Figure at $I_C = 200\text{ }\mu\text{A}$, $V_{CE} = 5\text{ V}$, $R_G = 2\text{ K}\Omega$, $f = 1\text{ KHz}$ at $I_C = 200\text{ }\mu\text{A}$, $V_{CE} = 5\text{ V}$, $R_G = 2\text{ K}\Omega$, $f = 30 \sim 15\text{ KHz}$	BC846, BC847, BC848 NF BC849, BC850 NF BC849 NF BC850 NF	- NF - NF - NF -	- - - - - -	10 4 4 3	dB dB dB dB

