




LOW Voltage Trench Nch MOSFET
◆ Features:

- ✧ Fast switching speed
开关速度快
- ✧ Low gate charge
低门充电
- ✧ High power and current handling capability
高功率和电流处理能力
- ✧ RoHS compliant
符合 RoHS 标准

◆ Applications

- ✧ DC to DC converters
直流到直流转换
- ✧ Synchronous Rectification
同步整流


TO-252

1


单位:mm
TO-252

◆ Absolute Maximum Ratings (Tc=25°C)

Symbol	Parameters	Ratings	Unit
V _{DSS}	Drain-Source Voltage 漏源电压	40	V
V _{GS}	Gate-Source Voltage-Continuous 栅源电压	±20	V
I _D	Drain Current-Continuous (Note 2) 漏极持续电流	120	A
I _{DM}	Drain Current-Single Plused (Note 1) 漏极单次脉冲电流	480	A
P _D	Power Dissipation (Note 2) 功率损耗	88	W
T _j	Max.Operating junction temperature 最大结温	150	°C

◆ Electrical characteristics (Tc=25°C unless otherwise noted)

Symbo l	Parameters	Min	Typ	Max	Units	Conditions
Static Characteristics						
B _{VDSS}	Drain-Source Breakdown VoltageCurrent (Note 1) 漏极击穿电压	40	--	--	V	I _D =250μA, V _{GS} =0V
V _{GS(th)}	Gate Threshold Voltage 栅极开启电压	1.0	--	2.5	V	V _{DS} =V _{GS} , I _D =250μA
R _{DS(on)}	Drain-Source On-Resistance 漏源导通电阻	--	3.9	4.5	mΩ	V _{GS} =10V, I _D =1A
I _{GSS}	Gate-Body Leakage Current 栅极漏电流	--	--	±100	nA	V _{GS} =±25V, V _{DS} =0
I _{DSS}	Zero Gate Voltage Drain Current 零栅极电压漏极电流	--	--	1	μA	V _{DS} =30V, V _{GS} =0
g _{fs}	Forward Transconductance 正向跨导	--	12	--	S	V _{DS} =5V, I _D =10A

**OSD120N04T****LOW Voltage Trench Nch MOSFET**

Switching Characteristics						
T _{d (on)}	Turn-On Delay Time 开启延迟时间	--	14	--	ns	V _{GS} =10V, V _{DS} =25V,I _D =10A, R _G =1Ω
T _r	Rise Time 上升时间	--	19	--	ns	
T _{d (off)}	Turn-Off Delay Time 关闭延迟时间	--	47	--	ns	
T _f	Fall Time 下降时间	--	18	--	ns	
Q _g	Total Gate Charge 栅极总电荷	--	142	--	nC	V _{DS} =20V , V _{GS} =4.5V, I _D =20A
Q _{gs}	Gate-Source Charge 栅源极电荷	--	30	--	nC	
Q _{gd}	Gate-Drain Charge 栅漏极电荷	--	15	--	nC	
Dynamic Characteristics						
C _{iss}	Input Capacitance 输入电容	--	7500	--	pF	V _{DS} =20V, V _{GS} =0, f=1MHz
C _{oss}	Output Capacitance 输出电容	--	565	--	pF	
C _{rss}	Reverse Transfer Capacitance 反向传输电容	--	530	--	pF	
I _S	Continuous Drain-Source Diode Forward Current (Note 2) 二极管导通正向持续电流	--	--	120	A	
V _{SD}	Diode Forward On-Voltage 二极管正向导通电压	--	--	1.2	V	I _S =20A, V _{GS} =0
R _{th(j-c)}	Thermal Resistance, Junction to Case 结到外壳的热阻	--	--	1.42	°C/W	

Note 1: Repetitive Rating : Pulse width limited by maximum junction temperature

Note 2: Pulse test: PW ≤ 300us , duty cycle ≤ 2%.