

This document contains proprietary information and such information may not be disclosed to others for any purposes,
not used for sales/marketing/procurement purposes without written permission



REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	19/03/17	19/03/17

1 Electrical

- 1.1 Impedance: $50\ \Omega$
- 1.2 Frequency: DC~18GHz
- 1.3 VSWR: ≤ 1.30
- 1.4 Insulation resistance: $\geq 5000M\ \Omega$
- 1.5 Dielectric strength: 1000V
- 1.6 Contact resistance
 - Center contact $\leq 3.0M\ \Omega$
 - Outer contact $\leq 2.0M\ \Omega$

2 Materials&Finish

- 2.1 Inner Contact: Beryllium-Copper, Gold plated
- 2.2 Outer Contact: Brass, Gold plated
- 2.3 Insulators: PTFE



Notes:

1. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME
2. CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DRAWN: H.wei 19/03/17
ENGINEER: L.yu 19/03/17
APPROVED: W.yi 19/03/17
TOLERANCES UNLESS OTHERWISE SPECIFIED
X ± 0.50
.X ± 0.20
.XX ± 0.10
ANGLES $\pm 1^\circ$

TITLE:
RF Coaxial Connector
SMA Female Conn. PCB
Mount

PART NO: HL-SMA-KHDC5-GB-1



DIMENSION IN MILLIMETERS (mm)

SIZE: A4 SCALE: N/A SHEET: 1/1 REV: A