




## Bridge Recifiters

**Package : HBL**


- Glass passivated junction
- Ideal for printed circuit board application
- High surge current capability
- Meets MSL level1,per J-STD-020, LF maximum peak of 260°C

General purpose use in AC/DC bridge full wave rectification for SMPS, lighting ballaster, adapter, battery charger, home appliances, office equipment, and telecommunication applications.

- **Package:** HBL  
Molding compound meets UL 94 V-0 flammability rating, RoHS-compliant, Halogen-free
- **Terminals:** Tin plated leads, solderable per J-STD-002 and JESD22-B102
- **Polarity:** As marked on body



Dimensions in millimeters



| Parameter                                                                      |                              | Symbol     | HBL<br>15005 | HBL<br>1501 | HBL<br>1502 | HBL<br>1504 | HBL<br>1506 | HBL<br>1508 | HBL<br>1510 | unit               |
|--------------------------------------------------------------------------------|------------------------------|------------|--------------|-------------|-------------|-------------|-------------|-------------|-------------|--------------------|
| Maximum repetitive peak reverse voltage                                        |                              | $V_{RRM}$  | 50           | 100         | 200         | 400         | 600         | 800         | 1000        | V                  |
| Maximum RMS bridge input voltage                                               |                              | $V_{RMS}$  | 35           | 70          | 140         | 280         | 420         | 560         | 700         | V                  |
| Maximum DC blocking voltage                                                    |                              | $V_{DC}$   | 50           | 100         | 200         | 400         | 600         | 800         | 1000        | V                  |
| Average rectified output current<br>@60HZ sine wave, R-load, Tc=118℃           |                              | $I_O$      | 15.0         |             |             |             |             |             |             | A                  |
| Instantaneous forward<br>voltage drop per diode                                | $I_{FM}=1.0A$                | $V_F$      | 0.79 Typ.    |             |             |             | 0.82 Max.   |             |             | V                  |
|                                                                                | $I_{FM}=7.5A$                |            | 0.89 Typ.    |             |             |             | 0.93 Max.   |             |             |                    |
|                                                                                | $I_{FM}=15.0A$               |            | 0.95 Typ.    |             |             |             | 0.98 Max.   |             |             |                    |
| Forward Surge Current (Non-repetitive)<br>@60Hz Half-sine wave,1 cycle, Tj=25℃ |                              | $I_{FSM}$  | 400          |             |             |             |             |             |             | A                  |
| Forward Surge Current (Non-repetitive)<br>@1ms square wave,1 cycle, Tj=25℃     |                              |            | 800          |             |             |             |             |             |             |                    |
| Maximum DC reverse current at ratde TA=25℃                                     |                              | $I_R$      | 5            |             |             |             |             |             |             | μA                 |
| DC blocking voltage per element TA=125℃                                        |                              |            | 100          |             |             |             |             |             |             |                    |
| Rating for fusing(t<8.3ms)                                                     |                              | $I^2t$     | 664.0        |             |             |             |             |             |             | A <sup>2</sup> sec |
| Thermal<br>resistance                                                          | Between Junction and Ambient | $R_{eJ-A}$ | 50           |             |             |             |             |             |             | ℃/w                |
|                                                                                | Between Junction and Lead    | $R_{eJ-L}$ | 10           |             |             |             |             |             |             |                    |
|                                                                                | Between Junction and Case    | $R_{eJ-C}$ | 2            |             |             |             |             |             |             |                    |
| Operating junction and stroage temperature range                               |                              | $T_J$      | -55to+150    |             |             |             |             |             |             | ℃                  |
|                                                                                |                              | $T_{STG}$  |              |             |             |             |             |             |             |                    |

Characteristics (Typical)

**HBL15005 THRU HBL1510**

FIG1:Io-Tc Curve




FIG2:Surge Forward Current Capability




FIG3:Typical Reverse Characteristics




FIG4: Typical Forward Voltage

