



20A SCHOTTKY BARRIER RECTIFIER

MBRD20150CT

Features:

- ☐ Low power loss, high efficiency.
High surge capacity
- ☐ For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications.
- ☐ Metal silicon junction, majority carrier conduction.
- ☐ High current Capability, low forward voltage drop.
- ☐ Guard ring for over voltage protection.

TO-252



Absolute Maximum Ratings (Ta=25°C unless otherwise noted)

Parameter		Symbol	Value	Unit
Maximum Recurrent Peak Reverse Voltage		V_{RRM}	200	V
Maximum RMS Voltage		V_{RMS}	140	V
Maximum DC Blocking Voltage		$V_{R(DC)}$	200	V
Maximum Average Forward Current		$I_{F(AV)}$	20	A
Peak Forward Surge Current: 8.3ms single half sine-wave superimposed on rated load (JEDEC method)		I_{FSM}	200	A
Maximum Forward Voltage @10A		V_F	0.95	V
Maximum DC Reverse Current	Tj=25°C	I_R	0.1	mA
	Tj=125°C		20	mA
Maximum Operating Junction Temperature		T_j	150	°C
Storage Temperature		T_{stg}	-50~+150	°C

Typical Characteristics

RATING AND CHARACTERISTIC CURVES




Fig.1 FORWARD CURRENT ERATING CURVE




Fig.2 MAXIMUM NON-REPETITIVE SURGE CURRENT




Fig.3 TYPICAL REVERSE CHARACTERISTIC





Fig.4 TYPICAL INSTANTANEOUS FORWARD CHARACTERISTIC

Package Dimension

TO-252

Unit:mm



Symbol	Dimensions In Millimeters		Symbol	Dimensions In Millimeters	
	Min	Max		Min	Max
A	2.20	2.40	E	5.95	6.25
B	0.95	1.25	e1	2.24	2.34
b	0.70	0.90	e2	4.43	4.73
b1	0.45	0.55	L1	9.85	10.35
C	0.45	0.55	L2	1.25	1.75
D	6.45	6.75	L3	0.60	0.90
D1	5.20	5.40	K	0.00	0.10