

## 1MHZ CMOS Rail-to-Rail IO Opamp with RF Filter

### Features

- Single-Supply Operation from +2.1V ~ +5.5V
- Rail-to-Rail Input / Output
- Gain-Bandwidth Product: 1MHz (Typ.)
- Low Input Bias Current: 1pA (Typ.)
- Low Offset Voltage: 3.5mV (Max.)
- Quiescent Current: 40μA per Amplifier (Typ.)
- Operating Temperature: -40°C ~ +125°C
- Embedded RF Anti-EMI Filter



### Ordering Information

DEVICE	Package Type	MARKING	Packing	Packing Qty
LMV602N	DIP-8	LMV602	TUBE	2000pcs/Box
LMV602M/TR	SOP-8	LMV602	REEL	2500pcs/Reel
LMV602MM/TR	MSOP-8	LMV602,V602	REEL	3000pcs/Reel
LMV602DQ2/TR	DFN-8 2*2	LMV602	REEL	4000pcs/Reel

### General Description

The LMV602 have a high gain-bandwidth product of 1MHz, a slew rate of 0.6V/μs, and a quiescent current of 40μA/amplifier at 5V. The LMV602 is designed to provide optimal performance in low voltage and low noise systems. They provide rail-to-rail output swing into heavy loads. The input common mode voltage range includes ground, and the maximum input offset voltage is 3.5mV for LMV602. They are specified over the extended industrial temperature range (-40°C to +125°C). The operating range is from 2.1V to 5.5V. The LMV602 Dual is available in Green SOP-8, MSOP8, DIP-8 and DFN-8 packages.

### Applications

- ASIC Input or Output Amplifier
- Sensor Interface
- Medical Communication
- Smoke Detectors
- Audio Output
- Piezoelectric Transducer Amplifier
- Medical Instrumentation
- Portable Systems

## Pin Configuration



Figure 1. LMV602 Pin Assignment Diagram

## Absolute Maximum Ratings

Condition	Min	Max
Power Supply Voltage (V <sub>DD</sub> to V <sub>SS</sub> )	-0.5V	+7.5V
Analog Input Voltage (IN+ or IN-)	V <sub>SS</sub> -0.5V	V <sub>DD</sub> +0.5V
PDB Input Voltage	V <sub>SS</sub> -0.5V	+7V
Operating Temperature Range	-40°C	+125°C
Junction Temperature	+160°C	
Storage Temperature Range	-55°C	+150°C
Lead Temperature (soldering, 10sec)	+260°C	
Package Thermal Resistance (TA=+25°C)		
SOP-8, θJA	125°C/W	
MSOP-8, θJA	216°C/W	
ESD Susceptibility		
HBM	6KV	
MM	300V	

**Note:** Stress greater than those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions outside those indicated in the operational sections of this specification are not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

## Electrical Characteristics


(At  $V_S = +5V$ ,  $R_L = 100k\Omega$  connected to  $V_S/2$ , and  $V_{OUT} = V_S/2$ , unless otherwise noted.)

PARAMETER	SYMBOL	CONDITIONS	TYP	MIN/MAX OVER TEMPERATURE			
			+25°C	+25°C	-40°Cto+85°C	UNITS	MIN/MAX
INPUT CHARACTERISTICS							
Input Offset Voltage	V <sub>OS</sub>	V <sub>CM</sub> = VS/2	0.4	3.5	5.6	mV	MAX
Input Bias Current	I <sub>B</sub>		1			pA	TYP
Input Offset Current	I <sub>OS</sub>		1			pA	TYP
Common-Mode Voltage Range	V <sub>CM</sub>	V <sub>S</sub> = 5.5V	-0.1 to +5.6			V	TYP
Common-Mode Rejection Ratio	CMRR	V <sub>S</sub> =5.5V, V <sub>CM</sub> = -0.1V to 4V	70	62	62	dB	MIN
		V <sub>S</sub> =5.5V, V <sub>CM</sub> = -0.1V to 5.6V	68	56	55		
Open-Loop Voltage Gain	A <sub>OL</sub>	R <sub>L</sub> =5kΩ, V <sub>O</sub> = +0.1V to +4.9V	80	70	70	dB	MIN
		R <sub>L</sub> =10kΩ, V <sub>O</sub> =+0.1V to +4.9V	100	90	85		
Input Offset Voltage Drift	ΔV <sub>OS</sub> /ΔT		2.7			μV/°C	TYP
OUTPUT CHARACTERISTICS							
Output Voltage Swing from Rail	V <sub>OH</sub>	R <sub>L</sub> = 100kΩ	4.997	4.990	4.980	V	MIN
	V <sub>OL</sub>	R <sub>L</sub> = 100kΩ	3	10	20	mV	MAX
	V <sub>OH</sub>	R <sub>L</sub> = 10kΩ	4.992	4.970	4.960	V	MIN
	V <sub>OL</sub>	R <sub>L</sub> = 10kΩ	8	30	40	mV	MAX
Output Current	I <sub>SOURCE</sub>	R <sub>L</sub> = 10Ω to VS/2	84	60	45	mA	MIN
	I <sub>SINK</sub>		75	60	45		
POWER SUPPLY							
Operating Voltage Range				2.1	2.5	V	MIN
				5.5	5.5	V	MAX
Power Supply Rejection Ratio	PSRR	V <sub>S</sub> = +2.5V to +5.5V, V <sub>CM</sub> = +0.5V	82	60	58	dB	MIN
Quiescent Current / Amplifier	I <sub>Q</sub>		40	60	80	μA	MAX
DYNAMIC PERFORMANCE (CL = 100pF)							
Gain-Bandwidth Product	GBP		1			MHz	TYP
Slew Rate	SR	G = +1, 2V Output Step	0.6			V/μs	TYP
Settling Time to 0.1%	t <sub>s</sub>	G = +1, 2V Output Step	5			μs	TYP
Overload Recovery Time		V <sub>IN</sub> ·Gain = VS	2.6			μs	TYP
NOISE PERFORMANCE							
Voltage Noise Density	e <sub>n</sub>	f = 1kHz	27			nV /√Hz	TYP
		f = 10kHz	20			nV/√Hz	TYP


## Typical Performance characteristics

At  $T_A = +25^\circ\text{C}$ ,  $V_S = +5\text{V}$ , and  $R_L = 100\text{K}\Omega$  connected to  $V_S/2$ , unless otherwise noted.


Large-Signal Step Response




Small-Signal Step Response




Supply Current vs. Supply Voltage




Short-Circuit Current vs. Supply Voltage



Output Voltage vs. Output Current




Output Voltage vs. Output Current




## Typical Performance characteristics

At  $T_A = +25^\circ\text{C}$ ,  $V_S = +5\text{V}$ , and  $R_L = 100\text{K}\Omega$  connected to  $V_S/2$ , unless otherwise noted.


Overload Recovery Time




Supply Current vs. Temperature




Input Voltage Noise Spectral Density vs. Frequency




Open Loop Gain, Phase Shift vs. Frequency at +5V



CMRR vs. Frequency



PSRR vs. Frequency



## Application Note

### Power Supply Bypassing and Board Layout

LMV602 series operates from a single 2.1V to 5.5V supply or dual  $\pm 1.05\text{V}$  to  $\pm 2.75\text{V}$  supplies. For best performance, a  $0.1\mu\text{F}$  ceramic capacitor should be placed close to the VDD pin in single supply operation. For dual supply operation, both VDD and VSS supplies should be bypassed to ground with separate  $0.1\mu\text{F}$  ceramic capacitors.

### Low Supply Current

The low supply current (typical  $40\mu\text{A}$  per channel) of LMV602 will help to maximize battery life. They are ideal for battery powered systems

### Operating Voltage

LMV602 operates under wide input supply voltage (2.1V to 5.5V). In addition, all temperature specifications apply from  $-40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ . Most behavior remains unchanged throughout the full operating voltage range. These guarantees ensure operation throughout the single Li-Ion battery lifetime

### Rail-to-Rail Input

The input common-mode range of LMV602 extends  $100\text{mV}$  beyond the supply rails ( $\text{VSS}-0.1\text{V}$  to  $\text{VDD}+0.1\text{V}$ ). This is achieved by using complementary input stage. For normal operation, inputs should be limited to this range.

### Rail-to-Rail Output

Rail-to-Rail output swing provides maximum possible dynamic range at the output. This is particularly important when operating in low supply voltages. The output voltage of LMV602 can typically swing to less than  $5\text{mV}$  from supply rail in light resistive loads ( $>100\text{k}\Omega$ ), and  $30\text{mV}$  of supply rail in moderate resistive loads ( $10\text{k}\Omega$ ).

### Capacitive Load Tolerance

The LMV602 is optimized for bandwidth and speed, not for driving capacitive loads. Output capacitance will create a pole in the amplifier's feedback path, leading to excessive peaking and potential oscillation. If dealing with load capacitance is a requirement of the application, the two strategies to consider are (1) using a small resistor in series with the amplifier's output and the load capacitance and (2) reducing the bandwidth of the amplifier's feedback loop by increasing the overall noise gain. Figure 2. shows a unity gain follower using the series resistor strategy. The resistor isolates the output from the capacitance and, more importantly, creates a zero in the feedback path that compensates for the pole created by the output capacitance.




Figure 2. Indirectly Driving a Capacitive Load Using Isolation Resistor

The bigger the  $R_{ISO}$  resistor value, the more stable  $V_{OUT}$  will be. However, if there is a resistive load  $R_L$  in parallel with the capacitive load, a voltage divider (proportional to  $R_{ISO}/R_L$ ) is formed, this will result in a gain error.

The circuit in Figure 3 is an improvement to the one in Figure 2.  $R_F$  provides the DC accuracy by feed-forward the  $V_{IN}$  to  $R_L$ .  $C_F$  and  $R_{ISO}$  serve to counteract the loss of phase margin by feeding the high frequency component of the output signal back to the amplifier's inverting input, thereby preserving the phase margin in the overall feedback loop. Capacitive drive can be increased by increasing the value of  $C_F$ . This in turn will slow down the pulse response.





Figure 3. Indirectly Driving a Capacitive Load with DC Accuracy



## Physical Dimensions


### SOP-8



Dimensions In Millimeters(SOP-8)

Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	1.35	0.05	4.90	5.80	3.80	0.40	0°	0.35	1.27 BSC
Max:	1.55	0.20	5.10	6.20	4.00	0.80	8°	0.45	

### DIP-8




Dimensions In Millimeters(DIP-8)

Symbol:	A	B	D	D1	E	L	L1	a	b	c	d
Min:	6.10	9.00	8.10	7.42	3.10	0.50	3.00	1.50	0.85	0.40	2.54 BSC
Max:	6.68	9.50	10.9	7.82	3.55	0.70	3.60	1.55	0.90	0.50	




## Physical Dimensions

### MSOP-8



Dimensions In Millimeters(MSOP-8)									
Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	0.80	0.05	2.90	4.75	2.90	0.35	0°	0.25	0.65 BSC
Max:	0.90	0.20	3.10	5.05	3.10	0.75	8°	0.35	

### DFN-8 2\*2



Dimensions In Millimeters(DFN-8 2*2)								
Symbol:	A	A1	B	B1	E	F	a	b
Min:	0.85	0	1.90	1.90	0.15	0.25	0.18	0.50TYP
Max:	0.95	0.05	2.10	2.10	0.25	0.45	0.30	

## Revision History

REVISION NUMBER	DATE	REVISION	PAGE
V1.0	2014-6	New	1-11
V1.1	2018-8	Update encapsulation type、Updated DIP-8 dimension	1、 8
V1.2	2024-11	Update Lead Temperature	2

**IMPORTANT STATEMENT:**

Huaguan Semiconductor reserves the right to change its products and services without notice. Before ordering, the customer shall obtain the latest relevant information and verify whether the information is up to date and complete. Huaguan Semiconductor does not assume any responsibility or obligation for the altered documents.

Customers are responsible for complying with safety standards and taking safety measures when using Huaguan Semiconductor products for system design and machine manufacturing. You will bear all the following responsibilities: Select the appropriate Huaguan Semiconductor products for your application; Design, validate and test your application; Ensure that your application meets the appropriate standards and any other safety, security or other requirements. To avoid the occurrence of potential risks that may lead to personal injury or property loss.

Huaguan Semiconductor products have not been approved for applications in life support, military, aerospace and other fields, and Huaguan Semiconductor will not bear the consequences caused by the application of products in these fields. All problems, responsibilities and losses arising from the user's use beyond the applicable area of the product shall be borne by the user and have nothing to do with Huaguan Semiconductor, and the user shall not claim any compensation liability against Huaguan Semiconductor by the terms of this Agreement.

The technical and reliability data (including data sheets), design resources (including reference designs), application or other design suggestions, network tools, safety information and other resources provided for the performance of semiconductor products produced by Huaguan Semiconductor are not guaranteed to be free from defects and no warranty, express or implied, is made. The use of testing and other quality control technologies is limited to the quality assurance scope of Huaguan Semiconductor. Not all parameters of each device need to be tested.

The documentation of Huaguan Semiconductor authorizes you to use these resources only for developing the application of the product described in this document. You have no right to use any other Huaguan Semiconductor intellectual property rights or any third party intellectual property rights. It is strictly forbidden to make other copies or displays of these resources. You should fully compensate Huaguan Semiconductor and its agents for any claims, damages, costs, losses and debts caused by the use of these resources. Huaguan Semiconductor accepts no liability for any loss or damage caused by infringement.