

Plastic-Encapsulate Transistors

TRANSISTOR (NPN)

FEATURES


- Complementary to MMBT4403T
- Small Surface Mount Package

MARKING: 2X

MAXIMUM RATINGS ($T_a=25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{CBO}	Collector-Base Voltage	60	V
V_{CEO}	Collector-Emitter Voltage	40	V
V_{EBO}	Emitter-Base Voltage	6	V
I_C	Collector Current	600	mA
P_C	Collector Power Dissipation	150	mW
$R_{\theta JA}$	Thermal Resistance From Junction To Ambient	625	$^{\circ}\text{C/W}$
T_j	Junction Temperature	150	$^{\circ}\text{C}$
T_{stg}	Storage Temperature	-55~+150	$^{\circ}\text{C}$

SOT-523



ELECTRICAL CHARACTERISTICS ($T_a=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C=100\mu\text{A}$, $I_E=0$	60			V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C=1\text{mA}$, $I_B=0$	40			V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E=100\mu\text{A}$, $I_C=0$	6			V
Collector cut-off current	I_{CBO}	$V_{CB}=35\text{V}$, $I_E=0$			100	nA
Collector cut-off current	I_{CEO}	$V_{CE}=35\text{V}$, $I_B=0$			500	nA
DC current gain	h_{FE}	$V_{CE}=1\text{V}$, $I_C=100\mu\text{A}$	20			
		$V_{CE}=1\text{V}$, $I_C=1\text{mA}$	40			
		$V_{CE}=1\text{V}$, $I_C=10\text{mA}$	80			
		$V_{CE}=1\text{V}$, $I_C=150\text{mA}$	100		300	
		$V_{CE}=2\text{V}$, $I_C=500\text{mA}$	40			
Collector-emitter saturation voltage	$V_{CE(sat)}$	$I_C=150\text{mA}$, $I_B=15\text{mA}$			0.4	V
		$I_C=500\text{mA}$, $I_B=50\text{mA}$			0.75	V
Base-emitter saturation voltage	$V_{BE(sat)}$	$I_C=150\text{mA}$, $I_B=15\text{mA}$	0.75		0.95	V
		$I_C=500\text{mA}$, $I_B=50\text{mA}$			1.2	V
Transition frequency	f_T	$V_{CE}=10\text{V}$, $I_C=20\text{mA}$, $f=100\text{MHz}$	250			MHz
Collector output capacitance	C_{ob}	$V_{CB}=5\text{V}$, $I_E=0$, $f=1\text{MHz}$			6.5	pF

Typical Characteristics

