



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASED	12APR2023	H.G	C.P



1. MATERIAL: COPPER ALLOY.
2. 0.38µm MIN GOLD PLATE IN LOCALIZED GOLD PLATE AREA, 2.5µm MIN TIN PLATE IN LOCALIZED TIN PLATE AREA,
3. CENTER CONTACT WILL ACCEPT COAXIAL CABLE: SEE TABLE.
4. 4-2326900-5 AS SHOWN.
5. PACKAGED ON REEL.

2.13	2.28	1.00	2	RG-58 LL	4-2326900-7
1.89	2.03	0.85	2	RTK-031, 2DS-PPFW(TA), RTK044	4-2326900-5
1.42	1.57	0.55	2	1.5DS, DACAR 363, DACAR 462, RG-174, RG-174 LL, RG-316	4-2326900-3
C	B	A	FINISH	APPLICABLE CABLE SIZE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.GUO 12-Apr-23	 TE Connectivity		
		CHK D.ZHU 12-Apr-23			
		APVD C.PAN 12-Apr-23			
		PRODUCT SPEC 108-32107			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME CENTER CONTACT, FEMALE, 180 DEGREE, FAKRA AUTOMATED		
		0 PLC ±0.5	SIZE A3		
		1 PLC ±0.13	CAGE CODE 00779		
		2 PLC ±0.013	DRAWING NO C-C-2326900		
		3 PLC ±0.0001	RESTRICTED TO -		
		4 PLC ±0.0001			
MATERIAL -		FINISH -	SCALE 10:1		
		finish_spec_2	SHEET 1 OF 1		
			REV A		
			CUSTOMER DRAWING		