

CMH50N60/CMA50N60

600V, 150mΩ typ., 50A N-Channel MOSFET

General Description

These Power MOSFETs are produced using Cmos's proprietary, planar stripe, DMOS technology. These devices are well suited for high efficiency switch mode power supply.

Product Summary

BVDSS	R _{DS(on)} max.	ID
600V	180mΩ	50A


Applications

- DC-DC converters
- Uninterruptible Power Supply

TO-247/TO-3P Pin Configuration

Features

- 100% avalanche tested
- Improve dv/dt capability
- RoHS compliant



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V _{DS}	Drain-Source Voltage	600	V
V _{GS}	Gate-Source Voltage	±30	V
I _D @T _C =25°C	Continuous Drain Current	50	A
I _D @T _C =100°C	Continuous Drain Current	35	A
I _{DM}	Pulsed Drain Current	200	A
EAS	Single Pulse Avalanche Energy (Note 1)	5120	mJ
P _D @T _C =25°C	Total Power Dissipation	600	W
T _{STG}	Storage Temperature Range	-55 to 150	°C
T _J	Operating Junction Temperature Range	150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
R _{θJA}	Thermal Resistance Junction-ambient	---	50	°C/W
R _{θJC}	Thermal Resistance Junction-case	---	0.21	°C/W

CMH50N60/CMA50N60

600V, 150mΩ typ., 50A N-Channel MOSFET

Electrical Characteristics (T_J=25°C , unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V , I _D =250μA	600	---	---	V
R _{DS(ON)}	Static Drain-Source On-Resistance	V _{GS} =10V , I _D =20A	---	150	180	mΩ
V _{GS(th)}	Gate Threshold Voltage	V _{GS} =V _{DS} , I _D =250μA	2	---	4	V
I _{DSS}	Drain-Source Leakage Current	V _{DS} =600V , V _{GS} =0V	---	---	10	μA
I _{GSS}	Gate-Source Leakage Current	V _{GS} = ±30V , V _{DS} =0V	---	---	±250	nA
g _{fs}	Forward Transconductance	V _{DS} =20V , I _D =20A	---	45	---	S
R _g	Gate Resistance	V _{DS} =0V , V _{GS} =0V , f=1MHz	---	0.8	---	Ω
Q _g	Total Gate Charge	V _{DD} =300V , I _D =25A V _{GS} =10V	---	---	---	nC
Q _{gs}	Gate-Source Charge		---	---	---	
Q _{gd}	Gate-Drain Charge		---	---	---	
T _{d(on)}	Turn-On Delay Time	V _{DS} =300V , I _D =25A R _G =10Ω , V _{GS} =10V	---	---	---	ns
T _r	Rise Time		---	---	---	
T _{d(off)}	Turn-Off Delay Time		---	---	---	
T _f	Fall Time		---	---	---	
C _{iss}	Input Capacitance	V _{DS} =100V , V _{GS} =0V , f=1MHz	---	8950	---	pF
C _{oss}	Output Capacitance		---	270	---	
C _{rss}	Reverse Transfer Capacitance		---	35	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I _S	Continuous Source Current	V _G =V _D =0V , Force Current	---	---	50	A
I _{SM}	Pulsed Source Current		---	---	200	A
V _{SD}	Diode Forward Voltage	V _{GS} =0V , I _S =40A , T _J =25°C	---	0.88	1.5	V
t _{rr}	Reverse Recovery Time	di/dt = 100A/μs	---	---	---	ns
Q _{rr}	Reverse Recovery Charge	V _{GS} =0V , I _{SD} =40A	---	---	---	μC

Note :

1. The EAS data shows Max. rating .The test condition is V_{DS}=120V , V_{GS}=10V , L=10mH , I_{AS}=32A.

This product has been designed and qualified for the consumer market.


Cmos assumes no liability for customers' product design or applications.

Cmos reserves the right to improve product design ,functions and reliability without notice.Please refer to the latest version of specification.


Package Dimension

TO-247

Unit :mm



符号	机械尺寸/mm			符号	机械尺寸/mm		
	最小值	典型值	最大值		最小值	典型值	最大值
A	4.80	5.00	5.20	E2		5.00	
A1	2.21	2.41	2.61	E3		2.50	
A2	1.90	2.00	2.10	e		5.44	
b	1.10	1.20	1.35	L	19.42	19.92	20.42
b1		2.00		L1		4.13	
b2		3.00		P	3.50	3.60	3.70
c	0.55	0.60	0.75	P1		7.19	
D	20.80	21.00	21.20	P2		2.50	
D1		16.55		Q		5.80	
D2		1.20		S	6.05	6.15	6.25
E	15.60	15.80	16.0	T		10.00	
E1		13.30		U		6.20	

Package Dimension
TO-3P
Unit :mm


Symbol	Dimensions	Symbol	Dimensions	Symbol	Dimensions
W	15.60±0.3	L	19.90±0.3	T	4.80±0.3
W1	13.60±0.3	L1	18.70±0.3	T1	1.50±0.3
W2	9.60±0.3	L2	13.90±0.3	T2	2.40±0.3
W3	5.45(TYP)	L3	5.00±0.3	T3	0.60±0.3
W4	1.00±0.3	L4	12.76±0.3	G	Ø3.25±0.3
W5	2.10±0.2	L5	3.50±0.3	G1	Ø3.58±0.3
W6	3.10±0.2	L6	20.00±0.3		