





REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD



PC Board Layout
Component Side Shown

Specifications:

1. Electrical:

Rated voltage and current: 125V 1.5A Max
Contact resistance: 50mΩ Max Initial state
100mΩ Max End state

Insulation resistance: 500MΩ Min

Withstand Voltage: AC 1000V

2. Mechanical:

Durability: 750Cycles 20-30Cycles/Min

3. Material:

Shell: 0.20mm Thickness Coper Alloy With Nikel Plated

Housing: Glass Filled Polyester UL94V-0

Contact: Phosphor Bronze

Plating: Gold Plating Fu " 50u " Over Nickel

4. Temperature Range: -25°C to +85°C.

5. Welding temperature: 260±5°C 3±0.5S

DETAIL LIST DIM (INCH) TOLERANCES EXCEPT AS NOTED .00 ± 0.05 .00 ± 0.05 .00 ± 0.05 ANGLES ± 0.5 THIRD ANGLE PROJECTION	DFTD 黄彬	DATE 2017.05.03	深圳市韩下电子有限公司 TITLE HX-RJ45 90 5631-1x1 8P8C DRAWING NO. TESJA1001 /PART NO. DO NOT SCALE DRAWING		
	CHKD 张伟	DATE 2017.05.03			
	MFO	DATE			
	APPVL 罗小睿	DATE 2017.05.03			
MATERIAL :			SIZE A3		
Q.T.Y :			REV 0		
FINISH :			SHEET X OF Y		
SCALE :					