





REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD



PC Board Layout
Component Side Shown

Specifications:

1. Electrical:

Rated voltage and current: 125V 1.5A Max

Contact resistance: 50mΩ Max Initial state
100mΩ Max End state

Insulation resistance: 500MΩ Min

Withstand Voltage: AC 1000V

2. Mechanical:

Durability: 750 Cycles 20-30Cycles/Min

3. Material:

Shell: 0.20mm Thickness Copper Alloy With Nickel Plated

Housing: Glass Filled Polyester UL94V-0

Contact: Phosphor Bronze

Plating: Gold Plating 50u " Over Nickel

4. Temperature Range: -25°C to +85°C.

5. Welding temperature: 260±5°C 3±0.5S

MM INCH TOLERANCES EXCEPT AS NOTED MM 0.15 * 0.00 0.075 * 0.00 0.05 *

ANGLES ± 0.5

THIRD ANGLE PROJECTION