

CMP035N12/CMB035N12/CMI035N12/CMF035N12

120V, 3.1mΩ typ., 180A N-Channel MOSFET

General Description

The 035N12 uses advanced SGT technology to provide excellent RDS(ON). This device is ideal for high-frequency switching and synchronous rectification.

Product Summary

BVDSS	R _{DS(on)} max.	ID
120V	3.5mΩ	180A


Applications

- Motor control and drive
- Battery management

Features

- Low On-Resistance
- 100% avalanche tested
- RoHS Compliant

TO-220/263/262/220F Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	220/263/262	220F	Units
V _{DS}	Drain-Source Voltage	120		V
V _{GS}	Gate-Source Voltage	±20		V
I _D @T _C =25°C	Continuous Drain Current	180	180*	A
I _D @T _C =100°C	Continuous Drain Current	126	126*	A
I _{DM}	Pulsed Drain Current	720	720*	A
EAS	Single Pulse Avalanche Energy (Note 1)	3610		mJ
P _D @T _C =25°C	Total Power Dissipation	300	45	W
T _{STG}	Storage Temperature Range	-55 to 150		°C
T _J	Operating Junction Temperature Range	-55 to 150		°C

* Drain current limited by maximum junction temperature.

Thermal Data

Symbol	Parameter	220/263/262	220F	Unit
R _{θJA}	Thermal Resistance Junction-ambient Max.(min.footprint)	62	62	°C/W
R _{θJC}	Thermal Resistance Junction-case Max.	0.42	2.78	°C/W

CMP035N12/CMB035N12/CMI035N12/CMF035N12

120V, 3.1mΩ typ., 180A N-Channel MOSFET

Electrical Characteristics ($T_J=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	120	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=10V$, $I_D=90A$	---	3.1	3.5	mΩ
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	2	---	4	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=120V$, $V_{GS}=0V$	---	---	1	uA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=10V$, $I_D=15A$	---	50	---	S
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	2.5	---	Ω
Q_g	Total Gate Charge	$V_{DS}=60V$, $I_D=90A$ $V_{GS}=10V$	---	147	---	nC
Q_{gs}	Gate-Source Charge		---	57.7	---	
Q_{gd}	Gate-Drain Charge		---	32.3	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=60V$ $R_{G_ext}=2.7\Omega$, $V_{GS}=10V$	---	33	---	ns
T_r	Rise Time		---	80	---	
$T_{d(off)}$	Turn-Off Delay Time		---	79	---	
T_f	Fall Time		---	47	---	
C_{iss}	Input Capacitance	$V_{DS}=25V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	9900	---	pF
C_{oss}	Output Capacitance		---	3600	---	
C_{rss}	Reverse Transfer Capacitance		---	320	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current	$V_G=V_D=0V$, Force Current	---	---	180	A
I_{SM}	Pulsed Source Current		---	---	720	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V$, $I_S=50A$	---	0.85	1.4	V
t_{rr}	Reverse Recovery Time	$V_{GS}=0V$, $I_S=90A$ $di/dt=100A/\mu s$	---	90.2	---	ns
Q_{rr}	Reverse Recovery Charge		---	240	---	nC

Note :







1.The EAS data shows Max. rating .The test condition is $V_{DS}=80V$, $V_{GS}=10V$, $L=5mH$, $I_{AS}=38A$.


This product has been designed and qualified for the counsumer market.

Cmos assumes no liability for customers' product design or applications.

Cmos reserver the right to improve product design ,functions and reliability wihtout notice.Please refer to the latest version of specification.

Typical Characteristics



Package Dimension
TO-220
Unit :mm


DIM	MILLIMETERS
A	10.0±0.3
A1	8.64±0.2
A2	1.15±0.1
A3	5.0±0.2
B	15.8±0.4
B1	13.2±0.3
C	4.56±0.1
C1	1.3±0.2
D	0.8±0.2
E	3.6±0.2
F	2.95±0.3
G	6.5±0.3
H	0.5±0.1
K	3.1±0.2
L	13.2±0.4
M	1.25±0.1
N	2.54±0.1
P	2.4±0.3
Q	9.0±0.3
T	W:0.35
DIA	⊙1.5 (deep 0.2)


CMP035N12/CMB035N12/CMI035N12/CMF035N12

120V, 3.1mΩ typ., 180A N-Channel MOSFET


Package Dimension

TO-263


Unit :mm



DIM	MILLIMETERS
A	9.8 ± 0.2
a	7.4 ± 0.4
B	4.5 ± 0.2
b1	1.3 ± 0.05
b2	2.4 ± 0.2
H	15.5 ± 0.3
h	1.54 ± 0.2
h1	10.5 ± 0.2
h2	9.2 ± 0.1
h3	1.54 ± 0.2
h4	2.7 ± 0.2
L	2.4 ± 0.2
1	1.3 ± 0.1
11	0.8 ± 0.1
12	1.3 ± 0.1
13	0.5 ± 0.1
N	2.54 ± 0.1
R	$0.5R \pm 0.05$

Package Dimension
TO-262
Unit :mm


DIM	MILLIMETERS
A	9.98 ± 0.2
a	7.4 ± 0.4
B	4.5 ± 0.2
b1	1.3 ± 0.05
b2	2.4 ± 0.2
H	23.9 ± 0.3
h	3.1 ± 0.2
h1	9.16 ± 0.2
h2	13.2 ± 0.2
L	0.5 ± 0.1
l1	1.3 ± 0.1
l2	0.8 ± 0.1
N	2.45 ± 0.1

Package Dimension
TO-220F
Unit :mm


DIM	MILLIMETERS
A	10.16 ± 0.3
A1	7.00 ± 0.1
A2	3.3 ± 0.2
A3	9.5 ± 0.2
B1	15.87 ± 0.3
B2	4.7 ± 0.2
B3	6.68 ± 0.4
C	3.3 ± 0.2
C1	12.57 ± 0.3
C2	10.02 ± 0.5
D	2.54 ± 0.05
D1	1.28 ± 0.2
D2	0.8 ± 0.1
K	3.1 ± 0.3
E1	2.54 ± 0.1
E3	0.5 ± 0.1
E4	2.76 ± 0.2
DIA	$\varnothing 1.5$ (deep 0.2)