




REV	ECN NO.	DATE

Specifications:

1. Electrical:
Rated voltage and current: 125V 1.5A Max
Contact resistance: 50mΩ Max Initial state
100mΩ Max End state
Insulation resistance: 500MΩ Min
Withstand Voltage: AC 1000V

2. Mechanical:
Durability: 750 Cycles 20-30Cycles/Min

3. Material:
Shell: Brass
Housing: LCP+15% G.F UL94V-0
Contact: Phosphor Bronze
Plating: Gold Plating Fu " 50u " Over Nickel

4. Temperature Range: -25℃ to +85℃. 5. Welding temperature: 260±5℃ 3±0.5S

e	LED			YELLOW	
d	LED			GREEN	
c	Shielding	1	Brass	Ni Plating	
f	COVER	1	LCP+15% G.F UL94V-0	BLACK	
b	Terminal	8	Phosphor Bronze	PLATING & COLOR	
a	Housing	1	LCP+15% G.F UL94V-0	BLACK	
NO.	PART NAME	Q'TY	MATERIAL	Material & Plating	Remark

TOLERANCES 公差		DATE 日期	2019-5-5		深圳市韩下电子有限公司	
mm		MATERIAL 材质			TITEL 品名	
.0±0.30	±	FINISH 电镀			PART NO. 料号	
.00±0.25	±				SIZE A4	
.000±0.10	±					
ANGLES ± 1°		SCALE 比例	1:1	UNIT 单位	mm	
THIRD ANGLE PROJECTION		Designed 设计	黄彬	Checked 审核	张伟	Approved 核准
					罗小春	SHEET OF