







PC Board Layout
Component Side Shown

Specifications:

1. Electrical:

Rated voltage and current: 125V 1.5A Max
Contact resistance: 50mΩ Max Initial state
100mΩ Max End state

Insulation resistance: 500MΩ Min
Withstand Voltage: AC 1000V

2. Mechanical:

Durability: 750 Cycles 20-30Cycles/Min

3. Material:

Shell: 0.20mm Thickness Coper Alloy With Nikel Plated
Housing: Glass Filled Polyester UL94V-0
Contact: Phosphor Bronze
Plating: Gold Plating Fu "50u" Over Nickel

4. Temperature Range: -25°C to +85°C.

5. Welding temperature: 260±5°C 3±0.5S

REVISION RECORD				
REV	ECO	DESCRIPTION	DRAFT	CHKD

MM INCH	DFTD 黄彬	DATE 2020.6.16
TOLERANCES EXCEPT AS NOTED	CHKD 张伟	DATE 2020.6.16
MM 0 ± 0.15 .00 ± 0.075 .000 ± 0.05	APPVL 罗小春	DATE 2020.6.16
ANGLES ± 0.5	Q.T.Y :	
THIRD ANGLE PROJECTION	FINISH :	
	SCALE :	

韩下 HANXIA 深圳市韩下电子有限公司		
TITLE HX-RJ45 90 5631-1x2 8P8C		
DRAWING NO. TESJA1007	SIZE A3	REV 0
/PART NO.		
DO NOT SCALE DRAWING		SHEET X OF Y