



深圳东裕光大电子有限公司
广州市东裕光电科技有限公司

产品规格书

SPECIFICATION

客户名称 CUSTOMER	
产品名称 PRODUCTION	红外接收管 Photo Transistor
产品型号 MODEL	ST-1CL3H(DYWH)
版本号 VERSION NO	A1.0

地址(Add): 深圳市光明区凤凰街道光明大道 481 号乐府广场 1B 栋 1609-1611 室

厂址(Add): 广东省广州市番禺区石基镇海涌路 3 号 10 号厂房 2 楼

电话(Tel): 18038161512

传真(Fax): 020-39966833

网址(Net): www.tonyuled.cn www.tonyuled.com



客户确认 CUSTOMER CONFIRMATION	审核 CHECKED BY	编制 PREPARED BY
	周毅兴	陈少龙

The ST-1CL3H(DYWH) is a high sensitivity NPN silicon phototransistor mounted in a 3Φ Low-cost ceramic package, designed for use as low-cost detector array in consumer and industrial applications.

Features


- Compact (Φ3mm)
- Wide angular response
- Low-cost

Applications

- Optical counters
- Optical detectors
- Floppy disk drives
- Encoders

Dimensions

[Unit : mm]



Absolute Maximum Ratings

[T_A = 25°C]

Parameter	Symbol	Rating	Unit
C-E Voltage	V _{CEO}	20	V
E-C Voltage	V _{ECO}	5	V
Collector current	I _C	20	mA
Collector power dissipation	P _C	75	mW
Operating temp	T _{opr.}	-20~+90	°C
Storage temp	T _{stg.}	-30~+100	°C
Soldering temp ^{*1}	T _{sol}	260	°C

*1. For MAX.5 seconds at the position of 2mm from the package


Electro-Optical Characteristics

[T_A = 25°C]


Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit.
Collector dark current	I _{CEO}	V _{CEO} =10V	-	1	200	nA
Light current	I _L	V _{CE} =3V, 1,000lx ^{*2}	0.08	1.5	-	mA
C-E saturation voltage	V _{CE(sat)}	I _C =0.2mA, 2,000lx ^{*2}	-	0.15	0.4	V
Switching speeds	Rise time	V _{CC} =10V, I _C =1mA R _L =100Ω	-	2.5	-	μsec
	Fall time		-	3.8	-	μsec
Spectral sensitivity	λ		480~1,000			nm
Peak wavelength	λ _p		-	880	-	nm
Half Angle	ΔΘ		-	±50	-	degrees

*2. Color temp = 2856K standard tungsten lamp


Collector current Vs.
Collector-Emitter voltage




Collector current Vs.
Illuminance




Dark current Vs.
Ambient temperature




Relative sensitivity Vs.
Wavelength



Switching time Vs.
Load resistance



Radiant Pattern



Collector power dissipation Vs.
Ambient temperature

