


BAT54 / A / C / S-HAF


Schottky Barrier Diodes

Features

- Halogen and Antimony Free(HAF), RoHS compliant



SOT-23 Plastic Package




Absolute Maximum Ratings ($T_a = 25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Value	Unit
Repetitive Peak Reverse Voltage	V_{RRM}	30	V
Average Rectified Forward Current	$I_{F(AV)}$	300	mA
Repetitive Peak Forward Surge Current at $t \leq 1\text{s}$, Duty ≤ 0.5 , Per diode	I_{FRM}	350	mA
Non-repetitive Peak Forward Surge Current at Pulse width = 1 second	I_{FSM}	600	mA
Power Dissipation	P_{tot}	290	mW
Operating Junction Temperature Range	T_j	- 55 to + 150	$^{\circ}\text{C}$
Storage Temperature Range	T_{stg}	- 55 to + 150	$^{\circ}\text{C}$

Thermal Resistance

Parameter	Symbol	Max.	Unit
Thermal Resistance Junction to Ambient ¹⁾	$R_{\theta JA}$	430	$^{\circ}\text{C/W}$


¹⁾ Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.



BAT54 / A / C / S-HAF

Characteristics at T_a = 25°C

Parameter	Symbol	Min.	Max.	Unit
Reverse Breakdown Voltage at I _R = 100 µA	V _{(BR)R}	30	-	V
Forward Voltage at I _F = 0.1 mA	V _F	-	240	mV
at I _F = 1 mA	V _F	-	320	mV
at I _F = 10 mA	V _F	-	400	mV
at I _F = 30 mA	V _F	-	500	mV
at I _F = 100 mA	V _F	-	800	mV
Reverse Current at V _R = 25 V	I _R	-	2	µA
Total Capacitance at V _R = 1 V, f = 1 MHz	C _{tot}	-	10	pF
Reverse Recovery Time at I _F = 10 mA, I _R = 10 mA, I _{RR} = 1 mA, R _L = 100 Ω	t _{rr}	-	5	ns



Electrical Characteristics Curves

Fig 1. Reverse Characteristics Curve




Fig 2. Forward Characteristics Curve




Fig 3. Junction Capacitance







Fig 4. Average Rectified Current Derating Curve



BAT54 / A / C / S-HAF


Package Outline (Dimensions in mm)

SOT-23



Unit	A	A1	B	C	D	E	F	G	L	L1
mm	1.20 0.89	0.100 0.013	1.40 1.20	0.19 0.08	3.04 2.80	2.6 2.2	1.02 0.89	2.04 1.78	0.51 0.37	0.2 MIN

Recommended Soldering Footprint




Packing information

Package	Tape Width (mm)	Pitch		Reel Size		Per Reel Packing Quantity
		mm	inch	mm	inch	
SOT-23	8	4 ± 0.1	0.157 ± 0.004	178	7	3,000

Marking information

" L4* " = Part No.

Type	Marking	Type	Marking
BAT54	L4	BAT54C	L43
BAT54A	L42	BAT54S	L44



" . " = HAF (Halogen and Antimony Free)

" YM " = Date Code Marking

" Y " = Year

" M " = Month

Font type: Arial

Disclaimer: Our company reserve the right to make modifications, enhancements, improvements, corrections or other changes to improve product design, functions and reliability, anytime without notice. Semtech Electronics Limited makes no warranties, representations or warranties regarding the suitability of its products for any particular purpose, and does not accept any liability arising from the application or use of any product or circuit such as: Apply to medical, military, aircraft, space or life support equipment and expressly waive any and all liability, including but not limited to special, consequential or collateral damage.

