



1. Designed for long haul Gigabit Ethernet 1000 Base-T, full duplex applications.
2. Supports four pairs of category 5 UTP cable.
3. Cable interface for isolation and low common mode emissions
4. Compliant with IEEE 802.3ab standard for 1000 Base-T
5. Operating Temperature range: 0 °C TO +70 °C
6. Storage temperature range: -25 °C TO +125 °C



DIMENSIONS & SCHEMATICS





Note: 1、Dimension: mm; 2.Unless otherwise specified,tolerances are: $\pm 0.15\text{mm}$;

TECHNICAL SPECIFICATIONS

OCL :	350 μH Min. @ 100 KHz, 100mV with 8mA DC Bias
Leakage Inductance:	0.5 μH Max. @ 100KHz, 0.1V
Cw/w:	112pF Max. @ 100KHz, 0.1V
DCR:	1.20 Ω Max.
Turns Ratio($\pm 5\%$):	1CT:1 (TX), 1CT:1 (RX)
Polarity:	1-72,3-70,5-68,7-66,10-63,12-61,14-59,16-57,19-54, 21-52,23-50,25-48, 28-45,30-43,32-41,34-39 In-Phase
Insertion Loss:	-1.1 dB Max. (TX & RX)@ 1-100 MHz
Return Loss:	-18 dB Min @ 0.5-30MHz -15 dB Min @ 40 MHz -13 dB Min @ 60 MHz -11 dB Min @ 80 MHz -10 dB Min.@ 100 MHz
Cross Talk:	-45 dB Min.@ 30 MHz -40 dB Min.@ 60 MHz -35 dB Min.@ 100 MHz
Common Mode Rejection :	-43 dB Min.@ 1-30 MHz -37 dB Min.@ 60 MHz -33 dB Min.@ 80-100 MHz
Isolation HI-POT:	1500Vrms 1mA 1Second

PACKING SPECIFICATION



EXPORT CARTON : 565*300*180

1. units/reel:14PCS
2. reel/carton:112PCS
3. units/carton :1568PCS