









TOLERANCE= ±0.05 THICKNESS=1.0mm



ECN NO	DISCRIPTION	DRAWN/DATE	CHEKED/DATE	APPROVED/DATE
A	NEW RELEASE	10 /01/16		

- SPECIFICATIONS:
- ELECTRICAL CHARACTERISTICS:
 - CURRENT RATING: 1.8A (PIN1,4) ; OTHER CONTACTS 0.25A
 - CONTACT RESISTANCE: 30m MAX. $\leq$
 - DIELECTRIC WITHSTANDING VOLTAGE: 100V AC FOR 1 MINUTE
 - INSULATION RESISTANCE: 100M MIN $\leq$
 - MECHANICAL CHARACTERISTICS:
 - INSERTION FORCE : 1.0~3.57 Kgf
 - WITHDRAWAL FORCE : 1.0~3.57 Kgf
 - DURABILITY: 1500 CYCLES.
 - TO CONFORM TO SINGATRON HAZARDOUS SUBSTANCE FREE SPEC.
 - HALOGEN PRODUCT IDENTIFICATION LABEL ON PACKAGING:
 - FOR REFLOW SOLDERING LEAD-FREE PROCESS.



REMARK	Pin Number	Signal ASSIGNMENT
USB2.0 CONTACT PIN	PIN 1	VBUS
	PIN 2	D-
	PIN 3	D+
	PIN 4	GND

D	MID SHELL	1	SPCC T=0.30	NICKEL 60u"MIN
C	TERMINAL	8	C2680 T=0.25	G/F ON MATING AREA. 100u"MIN TIN PLATED ON SOLDERING 50u"MIN NICKEL UNDER PLATING OVERALL
B	SHELL	1	SPCC T=0.30	NICKEL 60u"MIN
A	HOUSING	1	PBT UL94- V0	BLUE
NO	DESCRIPTION	QTY	MATERIAL	PLATING & COLOR

www.kinghelm.com.cn				
0755-28190160				
.X: ±0.25	.X: ±1°	APP.	DWG NO.	KH-2AF180-10JB
.XX: ±0.15	.X: ±0.5°	CHK.	TITLE:	USB A/F 双层直插10.0卷边
.XXX: ±0.10	.XX: ±0.02°	DGN.	19 /0 3/1_9	鱼叉式
UNIT: mm	SCALE: 1:1	DRW.	PART NO:	
REV. A	SHEET: 1/1			