






Kinghelm®



D	H
6.8	4.3
	5.0
	5.5
6.5	6.0
	6.5
	7.0
	7.5
	8.0
	8.5
	9.0
	9.5
	10.0
	10.5
6.0	11.0
	11.5
	12.0
	12.5
	13.0
	13.5
	14.0
	14.5
	15.0
	15.5
	16.0
	17.0
	18.0
	19.0



电 路 图



PCB. 焊接图



技术参数

1. 额定电流:50mA 12V DC
 2. 接触电阻:100毫欧
 3. 行 程:0.4±0.1 mm
 4. 绝缘电阻:100兆欧
 5. 耐电压:250v 50Hz 1Min

按力	$160 \pm 30\text{gf}$	$260 \pm 50\text{gf}$
寿命	10万次	10万次