

# TDS:EMIC

## 拓 電 半 導 體

自主封測 品質把控 售後保障


WEB | [WWW.TDSEMIC.COM](http://WWW.TDSEMIC.COM)




電源管理




顯示驅動




二三極管



LDO穩壓器




觸摸芯片



MOS管



運算放大器



存儲芯片



MCU



串口通信

## SMF3.3CA

產品規格說明書


### ■ Features

- Glass passivated chip
- 200W peak pulse power capability with a 10/1000  $\mu$ s waveform, repetitive rate (duty cycle):0.01%
- Low leakage
- Uni and Bidirectional unit
- Excellent clamping capability
- Very fast response time

### ■ Mechanical Data

- Case: Molded plastic
- Epoxy: UL 94V-0 rate flame retardant
- Lead: Solderable per MIL-STD-750, method 2026
- Polarity: Color band denotes cathode end except Bipolar
- Moisture Sensitivity: Level 1 per J-STD-020
- RoHS Compliant
- Whisker test is conducted based on JEDEC JESD201A per its table 4a and 4c
- IEC-61000-4-2 ESD 30kV(Air), 30kV (Contact)
- ESD protection of data lines in accordance with IEC 61000-4-2
- EFT protection of data lines in accordance with IEC 61000-4-4



### SOD-123FL



Dimensions: inch[mm]

Uni-directional

Bi-directional



### ■ Absolute Maximum Ratings ( $T_A=25^\circ\text{C}$ unless otherwise noted)

| Parameter                                                                       | Symbol                            | Value          | Unit             |
|---------------------------------------------------------------------------------|-----------------------------------|----------------|------------------|
| Peak power dissipation with a 10/1000 $\mu$ s waveform(1)                       | PPP                               | 200            | W                |
| Peak pulse current with a 10/1000 $\mu$ s waveform(1)                           | IPP                               | See Next Table | A                |
| Power dissipation on infinite heatsink at $T_L = 75^\circ\text{C}$              | PD                                | 0.4            | W                |
| Peak forward surge current, 8.3 ms single half sine-wave unidirectional only(2) | IFSM                              | 20             | A                |
| Maximum instantaneous forward voltage at 25 A for unidirectional only           | V <sub>F</sub>                    | 3.5            | V                |
| Operating junction and storage temperature range                                | T <sub>J</sub> , T <sub>STG</sub> | - 55 to +150   | $^\circ\text{C}$ |

Note:

(1)Non-repetitive current pulse per Fig.5 and derated above  $T_A= 25^\circ\text{C}$  per Fig.1

(2)Measured on 8.3 ms single half sine-wave or equivalent square wave, duty cycle = 4 pulses per minute maximum

### ■ Electrical Characteristics ( $T_A= 25^\circ\text{C}$ unless otherwise noted)

| Part Number<br>(Uni) | Part Number<br>(Bi) | Device<br>Marking<br>Code |    | Breakdown Voltage<br>VBR @IT |            |            | Maximum<br>Reverse<br>Leakage IR<br>@VRWM<br>( $\mu$ A) | Working<br>Peak<br>Reverse<br>Voltage<br>VRWM (V) | Maximum<br>Reverse<br>Surge<br>Current IPP<br>(A) | Maximum<br>Clamping<br>Voltage<br>VC @IPP<br>(V) |
|----------------------|---------------------|---------------------------|----|------------------------------|------------|------------|---------------------------------------------------------|---------------------------------------------------|---------------------------------------------------|--------------------------------------------------|
|                      |                     | Uni                       | Bi | Min<br>(V)                   | Max<br>(V) | IT<br>(mA) |                                                         |                                                   |                                                   |                                                  |
| SMF3.3A              | SMF3.3CA            | FD                        | KD | 5.2                          | 6.5        | 10         | 500                                                     | 3.3                                               | 22.7                                              | 8.8                                              |

### ■ Ratings and Characteristics Curves ( $T_A = 25^\circ\text{C}$ unless otherwise noted)




Fig. 1 - Pulse Derating Curve




Fig. 2 - Maximum Non-Repetitive Surge Current




Fig. 3 - Steady State Power Derating Curve




Fig. 4 - Peak Pulse Power Rating Curve




Fig. 5 - Pulse Waveform




Fig. 6 - Typical Junction Capacitance