

Specifications

备注(Remark)
1. 材料(MATERIAL)
胶芯: PA9T无卤料+30%G.F UL94V-0, 颜色:黑色.
Housing:PA9T无卤料+30%G.F UL94V-0, Color:Black
端子: 磷铜, 镍底30u", 表面接触点镀全金足0.8u"
Contact:Phosphor ,0.8u"MIN GOLD PLATING OVER ALL
30u" NICKEL UNDERPLATING OVER ALL



2. 特性 (characteristics):
额定电流: 3 AMP
Raring Current:3 AMP.
接触阻抗: 20 mΩ MAX.
Contact Resistance:20 mΩ MAX.
绝缘阻抗: 1000 MΩ MIN.
Insulating Resistance:1000 MΩ MIN.
耐电压: AC 500V/分钟.
Withstanding Voltage:AC 500V/Minute.
温度范围: -40° C to+105° C
Temperture Range: -40° C to+105° C

RoHS
COMPLIANT

客编: V1209

注意事项


- 带序号为必检尺寸,带*为重点检验尺寸
- 保持力0.3kg Min (公司标准)



Ordering Information

F136-12 06 A0 C MU B 1

NO. OF PINS PER ROW 2-40P	Contact Full of Gold A0=0.8u" A1=1u" A2=1.5u" A3=2u" A4=3u" A5=5u" A6=10u" A7=15u" A8=20u" A9=30u"	Plating Semi-gold B0=0.8u" B1=1u" B2=1.5u" B3=2u" B4=3u" B5=5u" B6=10u" B7=15u" B8=20u" B9=30u"	INSULATOR MATERIAL: B: PA9T C: PA9T D: LCP S1=Q di nary Tin Plated S2=Matte Tin Plated S3=Ti-n-pl ated High-temper ature	PACKING A: PE Bag B: Tape & Reel C: Tube D: Tube+CAP E: Tray
---------------------------------	---	--	---	---



OPERATION

SCALE

Fit

Yxcon

东莞市宇熙精密连接器有限公司
Dongguan Yuxi Electronic Co.,Ltd.

X.X ±0.25

UNIT

MM

X.XX ±0.20

SIZE

A4

SHEET

1/1

PROJ.

APPROVE

DESIGN

赵文品2025.02.11

PART NO.

F136-1206A0CMUB1

TITLE

2.54排母 3.6mm塑高 2*6P SMT:6.7 U型 磷铜 PA9T无卤
接触点镀全金足0.8u" 1000/卷+圆麦拉 V1209

Cust order No.

MODIFICATION DESCRIPTION

新版发行

DATE

SYMBOL

REV

A0

2025.02.22

/

1

2

3

4

5

6

7

8

9

10