

DFN1610-2L Plastic-Encapsulate ESD Protection Diodes


Features

- Low leakage current
- DFN1610-2L surface mount package
- IEC 61000-4-2 (ESD Air): ±25kV
- IEC 61000-4-2 (ESD Contact): ±25kV
- IEC 61000-4-5 (Lightning 8/20μs): 7.0A

Applications


- Mobile Phone, Digital cameras
- Battery Protection
- Power Line Protection
- Vbat pin for Mobile Devices
- Hand Held Portable Applications

Function Diagram



Reverse Working Voltage
5V Max.
Low capacitance
0.8pF(Max.)

DFN1610-2L




Maximum Ratings (Ta=25°C Unless otherwise specified)

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
V _{ESD}	Electrostatic Discharge Voltage	ESD per IEC 61000-4-2(Air)	±25	KV
		ESD per IEC 61000-4-2(Contact)	±25	KV
P _{PP}	Peak Pulse Power	tp = 8/20 μs	100	W
I _{PP}	Rated Peak Pulse Current	tp = 8/20 μs	7.0	A
T _J	Operating JunctionTemperature Range	—	-55 to +125	°C
T _{STG}	Operating JunctionTemperature Range	—	-55 to +125	°C

Electrical Parameter





SYMBOL	PARAMETER
V _C	Clamping Voltage @ I _{PP}
V _{BR}	Breakdown Voltage @ I _T
I _{PP}	Peak Pulse Current
I _T	Test Current
I _R	Reverse Leakage Current @ VRWM
V _{RWM}	Peak Reverse Working Voltage
P _{PP}	Peak Pulse Power Dissipation
C _J	Junction Capacitance @ V _R =0V,f=1MHz
I _F	Forward Current
V _F	Forward Voltage @I _F



● Electrical Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	CONDITION	Min	Typ	Max	UNIT
Peak Reverse Working Voltage	V_{RWM}	$T_a=25^{\circ}\text{C}$	—	—	5.0	V
Breakdown Voltage	V_{BR}	$I_R=1\text{mA}, T_a=25^{\circ}\text{C}$	6.0	8.0	—	V
Reverse Leakage Current	I_R	$V_R=5\text{V}, T_a=25^{\circ}\text{C}$	—	0.1	0.5	μA
Clamping Voltage	V_C	$I_{PP}=7\text{A}, t_p=8/20\mu\text{s}$	—	—	16	V
Junction Capacitance	C_J	$V_R=0\text{V}, f=1\text{MHz}$	—	0.7	0.8	pF


● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




● Ordering Information

PREFERED P/N	PACKAGE	SIZE(mm)	DELIVERY MODE	MPQ(PCS)
H5VL16B	DFN1610-2L	1.575×0.975×0.485	7" REEL	10000

● Recommended Soldering Conditions



● Package Outline Dimensions (DFN1610-2L)



● Suggested Pad Layout

