

Differential Probe PT-5250



Characteristic

- 2% accuracy.
- Adaptor power supply.
- Standard BNC interface, compatible with any brand's oscilloscope.

Model	PT-5250
Bandwidth(-3dB)	500X:DC-60MHz; 5000X:DC-20MHz
Attenuation Ratio	500X, 5000X
Accuracy	±2%
Input differential Vp-p	500X:5kV; 5000X:50kV
Input differential V AC RMS	17kV
Input differential V DC	500X:2.5kV; 5000X:25kV
Common mode voltage RMS	8.8kV
Rise Time	≥5.8ns
Input Impedance	140MΩ/3pF(Single-ended to ground); 280MΩ/1.5pF(Between the two ends)
Noise RMS	≤1mV
CMRR(Typical)	60Hz:>60dB; 100Hz:>50dB; 1MHz:>40dB
Oscilloscope input impedance	1MΩ
Power adaptor	9V DC
Temperature	0~50°C
Humidity	10~85% RH
Weight	488g
Dimension(L*W*H)	275x147x34mm

● ACCESSORIES



9V Adapter



BP-250



BP-266N



BP-276N



BP-366A(60cm)



extension cord(100cm)



Grounding wire

GUANGZHOU PINTECH CO.,LTD

Web:www.pintech.com.cn

Tel:020-82510899

E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.