

Differential Probe PT-8110



Characteristic

- 2% accuracy.
- Adaptor power supply.
- Standard BNC interface, compatible with any brand's oscilloscope.

Model	PT-8110
Bandwidth(-3dB)	100X:DC-50MHz; 1000X:DC-100MHz
Attenuation Ratio	100X, 1000X
Accuracy	±2%
Input differential Vp-p	100X:140V; 1000X:1400V
Input differential V AC RMS	490V
Input differential V DC	100X:70V; 1000X:700V
Common mode voltage RMS	490V
Rise Time	≥3.5ns
Impedance	4MΩ//1.18pF (Single-ended to ground); 8MΩ//0.59pF (Between the two ends)
Output	7V
RMS Noise	100X:<100mV; 1000X:<500mV
Oscilloscope input impedance	1MΩ
CMRR (typical)	60Hz>80dB; 100kHz>50dB
Options	6V DC/300mA mains adaptor
Length of BNC Cable	90cm
Length of Input Leads	30cm
Temperature	0~50°C
Humidity	20~75%RH
Weight	415g
Dimension(LxWxH)	187x83x41mm

● ACCESSORIES



Adapter



BP-368N

GUANGZHOU PINTECH CO.,LTD

Web:www.pintech.com.cn

Tel:020-82510899

E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.