




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECN-24-269412	06JUN2024	ED	WH



PCB MOUNTING HOLE

NOTES:

- PACK IN ACCORDANCE WITH TE SPEC 107-3275;
- ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED;
- ELECTRICAL CHARACTERISTICS :
FREQUENCY RANGE : DC-18GHz
NOMINAL IMPEDANCE : 50 OHMS
INSULATION RESISTANCE : 5000 MOHMS
WORKING VOLTAGE : 335 VRMS MAX
DIELECTRIC WITHSTANDING VOLTAGE : 750 VOLTS MAX
VSWR : 1.3(DC-18GHz)
CONTACT RESISTANCE :
CENTER CONTACT : 3 mOHMS MAX
OUTER CONTACT : 2 mOHMS MAX;
- MECHANICAL CHARACTERISTICS :
DURABILITY : 500 CYCLES
TORQUE SETTING : 7-10 IN-LBS;
- TEMPERATURE RANGE: -65°-+165°;
- TAPE AND REEL PACKAGING. PACKAGING DETAIL IS IN PAGE 2;
- RoHS: COMPLIANT.

	1	-	-	MYLAR	4
	1	GOLD 50u"/ NICKEL/COPPER	BERYLLIUM COPPER	CENTER CONTACT	3
	1	NATURAL	PTFE	INSULATOR	2
	1	GOLD 30u"/ NICKEL/COPPER	BRASS	BODY	1
	2466279-1	PLATING	MATERIAL	DESCRIPTION	ITEM
QUANTITY PER ASSY		PARTS LIST			




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ED 10SEP2023	TE Connectivity		
DIMENSIONS: mm		CHK ED 10SEP2023			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
	0 PLC ± 0.3		PRODUCT SPEC		
	1 PLC ± 0.2		APPLICATION SPEC		
	2 PLC ± 0.1		WEIGHT		
MATERIAL		APVD WH 10SEP2023	SIZE		
SEE TABLE		FINISH	CAGE CODE		
		-	DRAWING NO		
			RESTRICTED TO		
			SCALE		
			SHEET		
			REV		
			A1		

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

PACKAGING DETAIL

UNLESS OTHERWISE SPECIFIED
TOLERANCES

0.5-6	= ±0.2
6-30	= ±0.4
30-120	= ±0.6
120-315	= ±1
315-1000	= ±1.6
1000-2000	= ±2.4



- NOTE: 1. CARRIER TAPE : BLACK ANTI-STATIC POLYSTYRENE
APPROXIMATE LENGTH (METER) : 5.3M
2. COVER TAPE : TRANSPARENT ANTI-STATIC
PG-608B (21.3m/m)
3. BOX, CARTON : PAPER
4. QUANTITY : 300 PCS/BOX
1200 PCS/CARTON

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	10SEP2023	 TE Connectivity	
		ED	10SEP2023		
		CHK	10SEP2023		
		ED	10SEP2023		
		APVD	10SEP2023	NAME	
		PRODUCT SPEC		SMA JACK,PCB THROUGH HOLE, STRAIGHT,DC-18GHZ	
		APPLICATION SPEC			
		WEIGHT	0	SIZE	CAGE CODE
		CUSTOMER DRAWING		A2	00779
		SCALE	8:1	SHEET	2 OF 2
		REV	A1	RESTRICTED TO	