





REV.	SPECIFICATION	ECN NO.	APPD.
R5		BCN140328	



Material:

Housing: Thermoplastic Polyester Glass Filled UL94V-0

Contacts: Copper Alloy

Electrical Characteristics:

Current Rating: 2 AMP.

Dielectric Withstanding Voltage: AC 1000V for 1 minute.


Insulator Resistance: 1000MΩ min. at DC 500V.

Contact Resistance: 20mΩ max. at DC 100mA.


Operating Temperature: -55°C~+105°C .

***RoHS Compliant**

Insertion Depth: 2.55mm to 6.20mm.




Press Fit Type



Dip Type

Detail A



P.C. Board Layout
(Tolerance: ±0.05)

2044- 3 X xx G xx S P A

Series Triple Row No. of Pin Per Row G: Gold Plated T: Tin Plated

A: Tray Package B: Bulk Package P: Press Fit Type Blank: Dip Type S: Straight

00: G/F
10: 10"
15: 15"
30: 30"

Position Dimension	6 Thru 120
A	2.54 X No. of Position /3+0.4
B	2.54 X No. of Position /3-2.54

Tolerances	Dwg. No.	2044-D0000-005		Title: 2044 Series P.C.B. Socket 2.54mmX2.54mm(0.100"X0.100")		 深圳市格林柏电子技术开发有限公司				
x = ±0.5	Projection					P/N: 2044-3XxxGxxSPA				
.x = ±0.25	Unit	mm	Scale							1:1
.xx = ±0.15	Drawn By	ycj 03/15'16								
						SHRET	1/1	Ver. No.	R5	