

Differential Probe PT-5160M



Characteristic

- 2% accuracy.
- Adaptor power supply.
- Standard BNC interface, compatible with any brand's oscilloscope.

Model	PT-5160M
Bandwidth(-3dB)	DC-70MHz
Attenuation Ratio	100X, 1000X
Accuracy	±2%
Input differential Vp-p	100X:1600V; 1000X:16kV
Input differential V AC RMS	5.6kV
Input differential V DC	100X:800V; 1000X:8000V
Common mode voltage RMS	2.8kV
Rise Time	≥5ns
Input Impedance	10MΩ//10pF(Single-ended to ground); 20MΩ//5pF(Between the two ends)
Noise RMS	≤1mV
CMRR(Typical)	60Hz:>80dB; 100Hz:>60dB; 1MHz:>50dB
Oscilloscope input impedance	1MΩ
Power adaptor	5V DC
Temperature	0~50°C
Humidity	10~85% RH
Weight	450g
Dimension(L*W*H)	220x85x30mm

● ACCESSORIES



5V Adapter



BP-250



BP-266N



BP-276N



BP-366A

GUANGZHOU PINTECH CO.,LTD

Web:www.pintech.com.cn

Tel:020-82510899

E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.